

# Product data sheet

Specifications



## Floor standing enclosure polyester vers.PLA completely sealed 1250x1250x620 IP65

NSYPLA12126G

### Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLA
Nominal height	1250 mm
Nominal width	1250 mm
Nominal depth	620 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel

### Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Plain front
Number of doors	2 door(s)
Door opening side	Right and left (120 °)
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Rear Front
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
NEMA degree of protection	NEMA 13 NEMA 12 NEMA 2 NEMA 1
Product certifications	UL/cUL listed Veritas DNV Marine

Electrical insulation class	Class II
-----------------------------	----------

## Environment

IP degree of protection	IP65 conforming to IEC 60529 (completely sealed)
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	72.0 kg
Package 1 Height	128.0 cm
Package 1 width	128.0 cm
Package 1 Length	68.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>