



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: PCB Mount Header

PCB Mount Orientation: Right Angle

Connector System: Wire-to-Board

Number of Positions: 4

Number of Rows: 1

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Keying & Polarized Position Locations	2D
PCB Mount Orientation	Right Angle
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

--	--



Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.3 µm[51.18 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	3.8 µm[149.6 µin]
Mating Tab Width	6.3 mm[.248 in]
PCB Contact Termination Area Plating Material Thickness	3.8 µm[149.6 µin]
Contact Layout	Inline
Contact Base Material	Brass
Mating Tab Thickness	.8 mm[.032 in]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	16 A

Termination Features

Rectangular Termination Post & Tail Width	.8 mm[.032 in]
Rectangular Termination Post & Tail Thickness	.8 mm[.032 in]
Termination Post & Tail Length	3.8 mm[.149 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention	With
Mating Alignment Type	Keyed, Polarization
PCB Mount Alignment Type	Boss
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	5 mm[.197 in]



Dimensions

Connector Width	17.9 mm[.705 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]
Connector Height	14.9 mm[.59 in]
Connector Length	22.3 mm[.87 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	UL, VDE
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	112
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C











Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-521384-4 ASSY PL R/A RAST5 HEADER 04-C	 TE Part # 3-521384-4 ASSY PL R/A RAST5 HEADER 04-F	 TE Part # 3-521384-2 ASSY PL R/A RAST5 HEADER 02-E	 TE Part # 1-521384-4 ASSY PL R/A RAST5 HEADER 04-B
 TE Part # 5-521384-4 ASSY PL R/A RAST5 HEADER 4P	 TE Part # 521386-4 ASSY PL R/A RAST5 HDR 4P SP	 TE Part # 521385-4 ASSY DIN R/A RAST5 HEADER 04-A	 TE Part # 4-521384-2 ASSY PL R/A RAST5 HEADER 02-G
 TE Part # 1-521384-2 ASSY PL R/A RAST5 HEADER 02-B	 TE Part # 521384-4 ASSY PL R/A RAST5 HEADER 04-A	 TE Part # 521384-5 ASSY PL R/A RAST5 HEADER 05-B	

Also in the Series | RAST 5 IDC Connectors


 Connector Contacts(12)	 Crimp Terminal Housings(39)	 Insertion & Extraction Tools(1)	 PCB Headers & Receptacles(417)
---	--	--	---




Power Contacts(3)



Rectangular Power Connectors(481)



Standard Edge Connectors(31)



Wire-to-Board Headers & Receptacles (417)

Customers Also Bought



TE Part #521384-4
ASSY PL R/A RAST5 HEADER 04-A



TE Part #8-1437565-1
FSMCTATR=TACTILE SWITCH T&R



TE Part #3-2176339-7
CRGCQ 0603 10K 1%

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-521384-4_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-521384-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-521384-4_D.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_4-521384-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_4-521384-4_C.3d_stp.zip

English

Customer View Model

ENG_CVM_4-521384-4_C.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

FASTON PCB Tabs and Receptacles

English

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

RAST Connector System Catalog

English

Product Specifications

Product Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English

VDE Certificate

English