

8482-01

Torque wrench DREMOMETER SE with quick-fitting change

8-400 Nm / 70 lbf·in - 300 lbf·ft

Code **7714220** ETIM **EC002132**

EAN **4002805848210** UNSPSC **27-11-17-15**

Country of origin **Germany** eCI@ss **21-04-02-22**

Customs tariff number
82041100



Article description

- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/-3% deviation and thus with a greater precision than the standard-stipulated +/-4%
- Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- Drive offers extensive range of accessories
- Depending on the application, access is possible from the front (e.g. open-end fitting) or side (e.g. reversible ratchet and socket).
- Force to be applied in the middle of the handgrip only - do not use an extension tube as otherwise, inaccuracies can evolve
- Operation only with end fittings otherwise inaccuracies can arise. Keep the depth gauges on the certificate in mind. Only use original GEDORE accessories.
- Extremely low wear attributable to reduced forces in a lever mechanism
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use
- Long life cycles and tool lives
- Easy operation - fast and safe torque tightening
- Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
- With certificate acc. to DIN EN ISO 6789-2:2017, traceable via in-house DAkkS laboratory to national standards

Article information

Contents [Qty of pieces]	1	Precision +/-	+/- 3 %
Net weight [kg]	1,7 kg	Direction of tightening	Left and right
Total length [mm]	641 mm	Fixed setting	no
Total width [mm]	35 mm	Test certificate	DIN EN ISO 6789-2:2017
Total height [mm]	30 mm	Graduation	5
Material	Aluminum alloy	Head height 1 [mm]	30 mm
Depth gauge [metric]	25,0 mm	Width of head 1 [mm]	35,0 mm
Drive type/drive	Rectangular cavity	Torque wrench type	C-SE
Torque (min.) [N·m]	80 Nm	Calibration length	582 mm
Torque (max.) [N·m]	400 Nm	Graduation [lbf·ft]	5 lbf·ft
Torque (min.) [lbf·ft]	60 lbf·ft	Lever length drive side [mm]	53 mm
Torque (max.) [lbf·ft]	300 lbf·ft	Lever length handle side [mm]	588 mm
Torque range (min./max.) [N·m]	80 Nm - 400 Nm	Graduation [n·m]	5 Nm
Torque range (min./max.) [lbf·ft]	60 lbf·ft - 300 lbf·ft	Distance housing - square drive	16,5 mm
Drive connector rectangular	14 x 18 mm	Insertion depth 1	25,0 mm
Backup	Locking pin	Storage/Content	Plastic box
Trigger mechanism	Short path triggering		