

## Features

- Completely di-electric design, making it suitable for securing multiple energy isolation points and challenging-to-secure isolating devices.
- Molded PVC section designed to securely hold up to 12 padlocks simultaneously, providing group lockout capability.
- Incorporates solid stainless-steel inserts for added strength and durability, suitable for various environmental conditions.
- Designed to maintain a strong hold on the cable in all environmental conditions, enhancing safety during lockout procedures.

## RS PRO Universal Multipurpose Cable Lockout With 2 Mtrs. 4mm PVC Coated Steel Cable

RS Stock No.: 0276138



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- *Completely di-electric, suitable for securing multiple energy isolation points and difficult to secure isolating devices with ease.*
- *Moulded section in PVC to securely hold 12 padlocks at any given time.*
- *Incorporates solid stainless-steel inserts for added durability and strength.*
- *Supplied with a 2-meter cable of 4mm thickness.*
- *Strongly holds the PVC coated galvanized steel cable in all environmental conditions.*
- *Cable can withstand weights exceeding 100kg.*

## General Specifications

Type	Multipurpose Cable Lockout
Material	PVC Moulded Section with PVC coated galvanised steel cable
Number of Locks	12
Colour	Yellow & Black Body

## Mechanical Specifications

Length	71mm
Height	51mm
Cable thickness	4mm
Cable length	2 meters
Weight	130 Grams

## Operation Environment Specifications

Withstand temperature	-20°C to 70°C (-4°F to 158°F)
-----------------------	-------------------------------