

# 40mm Tower RO Pole Buzzer Flash

Local distributor code:

403034893 XVC4B25S

EAN Code: 3606480032486

## Main

Range of product	Harmony XVC4	
Product or component type	Complete pre-wired monolithic tower light	
Beacon or indicator bank unit type	2 illuminated units	
Sound signalling	Buzzer	
Mounting diameter	40 mm	
Component name	XVC	
Device short name	XVC	
Light source	LED steady or flashing red LED steady or flashing orange	
Supply circuit type	AC/DC	
Noise level	7085 dB (continuous or intermittent tone) at 1 m	

## Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover SGP (chromium-plated): support tube
Mounting location	On support tube, 17 mm
Product mounting	On support tube, 17 mm
[Us] rated supply voltage	24 V
[Us] rated supply voltage	24 V
Cable cross section	0.33 mm²
AWG gauge	AWG 22
Cable length	900 mm
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	90 mA
Fundamental frequency	2.23 kHz
Flashing frequency	1 Hz
Net weight	0.62 kg
Height	559.5 mm

## **Environment**

Standards	IEC 61000-6-2 IEC 61000-6-3	
Product certifications	UL	
Protective treatment	тс	
Ambient air temperature for storage	-3570 °C	
Ambient air temperature for operation	-1050 °C	
Electrical shock protection class	Class I conforming to IEC 61140	
Overvoltage category	Class I conforming to IEC 61140	
IP degree of protection	IP23 vertical surface installation conforming to IEC 60529	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.600 cm
Package 1 Width	6.600 cm
Package 1 Length	75.000 cm
Package 1 Weight	850.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	10
Package 2 Height	45.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	17.000 kg

# **Logistical informations**

Country of origin

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

### **Use Again**


○ Repack and remanufacture		
Take-back	No	

#### **Dimensions Drawings**

### Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

#### **Dimensions**

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.




No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	524.50	20.65
2 stages	559.50	22.03
3 stages	594.50	23.41
4 stages	629.50	24.78
5 stages	664.50	26.16

## XVC4B25S

Mounting and Clearance

## Pre-assembled and Pre-wired Tower Light

## **Support Tube Mounting**



### **Technical Illustration**

#### **Dimensions**

