

Specifications

Eaton EVMIFC20A

Eaton Metered Input G4 Rack PDU, 0U, 22.5U, C20 input, 3m cord, 1ph, 3.7kW, 16A, 200-240V, 24 outlets (12)C13, (12)C39



General specifications

PRODUCT NAME	Eaton Rack PDU G4
CATALOG NUMBER	EVMIFC20A
MODEL CODE	PDU G4 MI 0U C20 16A 1P 12xC13,12xC39
EAN	3553340697272
UPC	786689801403
PRODUCT LENGTH/DEPTH	1000 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	52 mm
PRODUCT WEIGHT	2.2 kg
COMPLIANCES	CB LVD Directive RoHS Directive WEEE Directive Packaging Directive EMC Directive
CERTIFICATIONS	UL 62368-1 cTUVus IEC 62368-1 EN IEC 63000 CE EAC UKCA Cm Ukr IEC/EN 61000-6-2 IEC/EN 61000-6-4 EN 61000-3-2 EN 61000-3-3 CISPR 35/EN 55035



Powering Business Worldwide

Electrical input

INPUT CONNECTION	C20
-------------------------	-----

WATTAGE	3.7 kW max
----------------	------------

AMPERAGE RATING	16A
------------------------	-----

INPUT VOLTAGE	200-240V
----------------------	----------

PHASE	Single-phase
--------------	--------------

FREQUENCY RATING	50/60 Hz
-------------------------	----------

CORD LENGTH	3m
--------------------	----

Electrical output

OUTLETS	(12) C13, (12) C39
----------------	--------------------

NUMBER OF OUTPUTS C13	12
----------------------------------	----

NUMBER OF OUTPUTS C19	12
----------------------------------	----

NUMBER OF OUTPUTS (OTHER)	12
--------------------------------------	----

NUMBER OF OUTLETS WITH EARTH PIN	24
---	----

Technology & communications

TYPE Metered input Rack PDU

OUTLET CONTROL No

SPECIAL FEATURES

- Remote Site Management
- Versatile C39 outlet supports C14 or C20 power cord plug
- High retention outlets designed to securely fit standard power cords and support P-Lock power cords
- Cybersecurity standards UL 2900-1 and IEC 62443-4-2
- Hot-Swap network control module
- Network Cascading, connect up to 32 PDUs via network loop
- Power sharing between two network modules PDUs ensures constant access to PDU data & sensors
- 1% IEC Class 1 billing grade measurement accuracy
- Gigabit network card with 2x Gb ports
- Support protocols RestAPI, Modbus TCP, SNMP, LDAP, HTTPS
- Optional sensor Temperature/Humidity

ETHERNET INTERFACE Yes

SERIAL INTERFACE Yes

SNMP Yes

MASS CONFIGURATION Yes

Resources

BROCHURES [Rack PDU G4 Brochure EN](#)

DECLARATIONS OF CONFORMITY [EU declaration of conformity Rack PDU G4](#)

Additional specifications

OPERATING TEMPERATURE 0° to 60°C (32° to 140°F)

ACCESSORIES

- Rack PDU
- Rack mounting accessories
- Quickstart guide
- Safety Instructions

MATERIAL Aluminium

COLOR Black

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

