



PRODUCT-DETAILS

OT160EV11**OT160EV11 SWITCH-DISCONNECTOR****General Information**

Extended Product Type	OT160EV11
Product ID	1SCA122726R1001
EAN	6417019536538
Catalog Description	OT160EV11 SWITCH-DISCONNECTOR
Long Description	OT160EV11 SWITCH-DISCONNECTOR

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301117M0201
Environmental Information	1SCC301265D0201
Environmental Product Declaration - EPD	1SCC301282D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301031M0220
Mechanical Drawings	1SCC301226F0001 1SCC301225F0001 OT200-250E11.stp OT200-250E11.igs
Environmental Product Declaration - EPD	1SCC301282D0201

Environmental

Degree of Protection	Front IP00
Environmental Information	1SCC301265D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	150 mm
Product Net Height	110.5 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	0.9 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	170 mm 6.7 in
Package Level 1 Depth / Length	190 mm 7.5 in
Package Level 1 Height	145 mm 5.7 in
Package Level 1 Gross Weight	1.1 kg 2.3 lb

Package Level 1 EAN

6417019536538

Technical

Conventional Thermal Current (I_{the})	Fully Enclosed 160 A
Degree of Protection	Front IP00
Handle Type	Handle and shaft not included
Mechanical Durability	20000
Mounting Type	Base mounting
Number of Poles	2P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 3.2 W
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 200 A (500 V) 200 A (690 V) 160 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 48 kW (400 ... 415 V) 88 kW (500 V) 112 kW (690 V) 144 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 30 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 8 kA
Special Functions	No
Standards	IEC 60947-3
Terminal Type	Lug terminals
Tightening Torque	acc. IEC 60947-1 15 ... 22 N·m

Technical UL/CSA

Tightening Torque	acc. IEC 60947-1 15 ... 22 N·m
-------------------	--------------------------------

Certificates and Declarations

A2L Certificate – IEC	1SCC301337D0201
Declaration of Conformity - CE	1SCC301131D2705
DNV GL Certificate	1SCC301174D0204

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnector (low voltage)
ETIM 10	EC000216 - Switch disconnector (AC)
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

