



- The integrally formed nylon pawl combines low insertion and high locking strength.
- A rounded, low-profile head makes for less snags.
- Tails have an improved two-sided finger grip design that helps the operator grasp and pull ties snug.
- “Sure Grip” tab keeps the tail from popping out while being threaded, then holds it securely for final tightening by hand or tool.
- Quick, easy pull through increases productivity, reduces operator fatigue.

From one end to the other, Ty-Fast® cable ties fit the needs of OEMs.

Designed with OEMs in mind, this new series of competitively priced Ty-Fast® cable ties holds down costs and speeds up cable fastening. Our all-nylon design lowers installation costs and provides features to ease fastening for harness fabrication and wire bundling in the manufacturing environment.

Ty-Fast® cable ties are made of nylon 6/6 and perform well in most applications in temperatures ranging from 185°F to -40°F. The smooth edges are designed to prevent damage to wire insulation, reducing the opportunity for shorting, and tails are “turned up” for fast assembly. Ty-Fast® cable ties come in natural or outdoor weatherable black, and custom colors and options are available.

Ty-Fast® cable ties may be fastened with standard Thomas & Betts tying tools. All your favorite Ty-Rap® mounting bases and accessories may be used with Ty-Fast® cable ties. For harsh industrial environments, use our “grip of steel” Ty-Rap® cable ties with the unique stainless steel barb. Ty-Rap® and Ty-Fast® cable ties combine to offer the most complete package of cable ties and accessories for the fastening market.

Ty-Fast® cable ties come in large poly bags for convenient inventory and easy access at the manufacturing site. Call your local Thomas & Betts distributor today and find out how well Ty-Fast® cable ties can fit your needs, from one end to the other.



Ty-Fast® Cable Ties

Cat. No.	Min. Tensile Strength (in lbs.)	Tie Length (in.)	Max. Bundle Diameter (in.)	Width (in.)	Std. Pkg. (pieces)
TY075-18	18	3.60	.75	.095	1000
TY125-18	18	5.34	1.25	.095	1000
TY125-40	40	5.60	1.25	.140	1000
TY200-18	18	7.75	2.00	.095	1000
TY200-40	40	8.00	2.00	.140	1000
TY200-120†	120	8.63	2.00	.299	500
TY300-40	40	11.40	3.00	.140	1000
TY175-50	50	7.30	1.75	.184	1000
TY300-50	50	11.40	3.00	.184	1000
TY400-50	50	14.30	4.00	.184	1000
TY400-120	120	14.30	4.00	.301	500

† Not or Recognized Models.



Outdoor Weatherable (black)

Cat. No.	Min. Tensile Strength (in lbs.)	Military Standard Part No.	Tie Length (in.)	Max. Bundle Diameter (in.)	Width (in.)	Std. Pkg. (pieces)
TY075-18X	18	—	3.60	.75	.095	1000
TY125-18X	18	—	5.34	1.25	.095	1000
TY125-40X	40	—	5.60	1.25	.140	1000
TY200-18X	18	—	7.75	2.00	.095	1000
TY200-40X	40	—	8.00	2.00	.140	1000
TY200-120X†	120	—	8.63	2.00	.299	500
TY300-40X	40	—	11.40	3.00	.140	1000
TY175-50X	50	—	7.30	1.75	.184	1000
TY300-50X	50	—	11.40	3.00	.184	1000
TY400-50X	50	—	14.30	4.00	.184	1000
TY400-120X†	120	—	14.30	4.00	.301	500

† Not or Recognized Models.