

Axicom

TE Internal #: 4-1393817-5

TE Internal Description: V23003B 37F104

Cradle P/W Signal Relay V23003

[View on TE.com >](#)



All Cradle P/W Signal Relay V23003 (0)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #163082-2
062 PIN ASS. TYP3+



TE Part #1623516-1
CRG1206 1% 470K



TE Part #4-2176231-6
3522 750R 1% 3W



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #1623426-1
CRG1206 1% 150K



TE Part #1623469-1
CRG1206 1% 270K



TE Part #100291-1
ADAPTER 90 M24/M27



TE Part #925256-1
40P MDM GEHAEUSE

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1393817-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1393817-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1393817-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Definitions General Purpose Relays

English