






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	00		A	ECR-14-002737	24FEB2014	KKB R,P
		A1	REVISED	PER ECR-14-012053	28AUG2014	AV KD
		A2	REVISED	PER ECR-15-002456	03MAR2015	AV DZ




- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
- SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
- DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
- FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION,OPTIONAL.
- UNDERWRITERS RECOGNIZED COMPONENT LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- TRADEMARK LOCATION (AMP OR TE CONNECTIVITY).
- MANUFACTURING LOCATION ID (OPTIONAL).
- MATERIAL CORRESPONDING TO THE REQUIREMENT OF IEC60335-1 (INCL. GLOW WIRE TEST 750° C WITHOUT FLAME)
- PRELIMINARY PART NOT RELEASED FOR PRODUCTION.
- NO LATCH WINDOW PRESENT.
- LATCH WINDOW PRESENT.




VIEW A-A
2178473-3 ONLY




DETAIL A
OPTIONAL CONSTRUCTION




DETAIL B
2178473-3 ONLY





2178473-3



27.43	1.080
20.32	.800
14.73	.580
11.68	.460
7.62	.300
0.38	.015
0.13	.005
MM	IN
CONVERSION TABLE	



8/11	PA66 UL94-V0 GWT750°C (NO FLAME)	NATURAL	2178473-3
8/10	PA66 UL94-V0 GWT750°C (NO FLAME)	NATURAL	2178473-2
9/10	PA6 UL94-V0	NATURAL	2178473-1
REMARKS	MATERIAL	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MGT	24JUN2013	 TE Connectivity	
		CHK R,P	24JUN2013		
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± .		PLUG, 3 CIRCUIT, UNIVERSAL MATE-N-LOK	
		1 PLC ± .			
		2 PLC ± 0.13 [.005]			
		3 PLC ± .			
		4 PLC ± .			
ANGLES		± 0°30'			
MATERIAL		FINISH		RESTRICTED TO	
SEE TABLE		-		-	
		CUSTOMER DRAWING		SIZE CAGE CODE DRAWING NO	
		WEIGHT		A1 00779 ©=2178473	
				SCALE 4:1 SHEET 1 of 1 REV A2	