


Symmetric Dual N-Channel 40 V (D-S) MOSFET

PowerPAIR® 6 x 5FSW



FEATURES


- TrenchFET® Gen IV power MOSFET
- 100 % R_g and UIS tested
- Integrated half-bridge MOSFET power stage
- Wettable flank terminals
- Internally connected switch node
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE
GRADE

RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Buck-boost
- Half-bridge synchronous rectification
- Synchronous buck
- Motor drive control



PRODUCT SUMMARY

V _{DS} (V)	40
R _{DS(on)} max. (Ω) at V _{GS} = 10 V	0.0015
R _{DS(on)} max. (Ω) at V _{GS} = 4.5 V	0.0024
I _D (A) ^e	162
Configuration	Dual

ORDERING INFORMATION

Package	PowerPAIR 6 x 5FSW
Lead (Pb)-free and halogen-free	SQZF140ELPW-T1_GE3

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-source voltage	V _{DS}	40	V
Gate-source voltage	V _{GS}	± 20	
Continuous drain current ^e	I _D	162	A
		93	
Pulsed drain current ^e	I _{DM}	543	
Continuous source-drain diode current ^e	I _S	68	
Single pulse avalanche current	I _{AS}	37	mJ
Single pulse avalanche energy	E _{AS}	68	
Maximum power dissipation ^{a, e}	P _D	75	W
		25	
Operating junction and storage temperature range	T _J , T _{stg}	-55 to +175	°C
Soldering recommendations (peak temperature) ^{d, e}		260	

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	LIMIT	UNIT
Junction-to-ambient	R _{thJA}	30	°C/W
Junction-to-case (exposed pad) ^d	R _{thJC}	2.0	

Notes

- Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2 %
- When mounted on 1" square PCB (FR4 material)
- See solder profile (www.vishay.com/doc?73257). The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection
- As per JESD51-14
- Values based on R_{thJC} and T_C of 25 °C. Actual values achievable will be dependent on the thermal characteristics of the complete system



SPECIFICATIONS (T _C = 25 °C, unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0, I _D = 250 μA		40	-	-	V
Gate-source threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA		1.2	1.7	2.2	
Gate-source leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V		-	-	± 100	nA
Zero gate voltage drain current	I _{DSS}	V _{GS} = 0 V	V _{DS} = 40 V	-	-	1	μA
		V _{GS} = 0 V	V _{DS} = 40 V, T _J = 125 °C	-	-	100	
		V _{GS} = 0 V	V _{DS} = 40 V, T _J = 175 °C	-	-	500	
Drain-source on-state resistance ^a	R _{DS(on)}	V _{GS} = 4.5 V	I _D = 15 A	-	0.00185	0.00240	Ω
		V _{GS} = 10 V	I _D = 15 A	-	0.00125	0.0015	
		V _{GS} = 10 V	I _D = 15 A, T _J = 125 °C	-	-	0.0024	
		V _{GS} = 10 V	I _D = 15 A, T _J = 175 °C	-	-	0.0030	
Forward transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 70 A		-	200	-	S
Dynamic ^b							
Input capacitance	C _{iss}	V _{GS} = 0 V	V _{DS} = 25 V, f = 1 MHz	-	5042	7059	pF
Output capacitance	C _{oss}			-	1096	1535	
Reverse transfer capacitance	C _{rss}			-	32	45	
Total gate charge	Q _g	V _{GS} = 10 V	V _{DS} = 20 V, I _D = 15 A	-	72	-	nC
Gate-source charge	Q _{gs}			-	15	-	
Gate-drain charge	Q _{gd}			-	12	-	
Gate resistance	R _g	f = 1 MHz		0.3	0.9	2.4	Ω
Turn-on delay time	t _{d(on)}	V _{DD} = 20 V, R _L = 1.33 Ω I _D ≡ 15 A, V _{GEN} = 10 V, R _g = 1 Ω		-	17	26	ns
Rise time	t _r			-	53	80	
Turn-off delay time	t _{d(off)}			-	40	60	
Fall time	t _f			-	8	12	
Source-Drain Diode Ratings and Characteristics ^b							
Body diode reverse recovery time	t _{rr}	I _F = 15 A, di/dt = 100 A/μs, T _J = 25 °C		-	42	84	ns
Body diode reverse recovery charge	Q _{rr}			-	38	76	nC
Reverse recovery fall time	t _a			-	22		A
Reverse recovery rise time	t _b			-	22		A
Pulsed current	I _{SM}			-	-	300	A
Forward voltage	V _{SD}	I _S = 10 A, V _{GS} = 0 V		-	0.75	1.1	V


Notes

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$
b. Guaranteed by design, not subject to production testing


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




Transfer Characteristics



On-Resistance vs. Drain Current




Transconductance




Capacitance




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Gate Charge




On-Resistance vs. Junction Temperature




Drain Source Breakdown vs. Junction Temperature



On-Resistance vs. Gate-to-Source Voltage



Source-Drain Diode Forward Voltage




Threshold Voltage

Note

- a. $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Note


b. $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)





Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?62496.

Recommended Land Pattern PowerPAIR® 6 x 5 FS and PowerPAIR® 6 x 5 FSW



Note

- Dimensions in mm

T24-0311-Rev. A, 09-Sep-2024
DWG: 3030



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.