

# NS212 SERIES CONNECTOR

**NS212 Series couplings** were built on the company's proven platform of non-spill valves designed to provide fast, safe and leak-free fluid line connections. The NS212 is an easy, twist-to-connect coupling with an integrated locking mechanism and double-sided non-spill shutoff valves. It is also chemically resistant and ideal for a diverse range of applications including printing and ink management, analytical instrumentation, electronic cooling and chemical handling. NS212 couplings provide high-flow fluid transfer in a small footprint.



## SPECIFICATIONS

### PRESSURE:

Vacuum to 45 psi, 3.1 bar

### TEMPERATURE:

32°F to 120°F (0°C to 49°C)

### MATERIALS:

**Main components:** Glass-filled polypropylene

**Valve spring:** 316 stainless steel

**Seal material:**

EPDM (FKM/Simriz® FFKM optional)

**COLOR:** Gray with black accent standard

### TUBING SIZES:

1/8" and 1/4" ID, 3.2 mm and 6.4 mm ID

**SPILLAGE:** <0.025 cc/disconnect

**INCLUSION:** 0.009 cc/connect

WARNING: Pressure, temperature, chemicals, and operating environment can affect the performance of couplings. It is the customer's responsibility to test the suitability of CPC products in their own application conditions.



[cpcworldwide.com/NS212](http://cpcworldwide.com/NS212)

### FEATURES

Efficient, non-spill design

Multiple seal materials

Twist-to-connect locking

Compact design

Ultra low air inclusion

### BENEFITS

Disconnect under pressure with no spills


Broad chemical compatibility for diverse applications

Easy, non-spill connections in tight spaces


High flow in a small connector

Minimizes contaminants, reduces the need to purge lines

**NS212 WATER FLOW**



**NS212 Pressure Range**



These graphs are intended to give you a general idea of the performance capabilities of each product line. The shaded area of each graph represents the operating range of the product family, i.e., upper and lower values are shown. Therefore, depending on the exact coupling configurations selected, you can reasonably expect values to fall within the shaded area.








**COLDER PRODUCTS COMPANY®**  
U.S.A.  
PHONE: +1 (651) 645-0091  
TOLL FREE: +1 (800) 444-2474  
E-MAIL: [info@cpcworldwide.com](mailto:info@cpcworldwide.com)

**COLDER PRODUCTS COMPANY GMBH**  
Germany  
E-MAIL: [cpcgmbh@cpcworldwide.com](mailto:cpcgmbh@cpcworldwide.com)



**DOVER (SHANGHAI) INDUSTRIAL CO., LTD**  
ShangHai, China  
PHONE: +86 21 2411 2666  
TOLL FREE: +86 400 990 1978  
E-MAIL: [asiapacific@cpcworldwide.com](mailto:asiapacific@cpcworldwide.com)

# NS212 SERIES DIMENSIONS

## COUPLING BODIES - Polypropylene

TERMINATION	TUBING/THREAD SIZE	METRIC EQ.	SHUTOFF	A	B
 IN-LINE PIPE THREAD	1/8" NPT		NS2D100212	0.71 (18.0)	1.74 (44.2)
 IN-LINE FERRULELESS POLYTUBE FITTING, PTF†	1/4" OD, .17 ID	6.4 mm OD, 4.3 mm ID	NS2D130412	0.71 (18.0)	1.87 (47.5)
 IN-LINE HOSE BARB	1/8" ID	3.2 mm ID	NS2D170212	0.71 (18.0)	1.87 (47.5)
	1/4" ID	6.4 mm ID	NS2D170412	0.71 (18.0)	2.05 (52.1)
 PANEL MOUNT FERRULELESS POLYTUBE FITTING, PTF†	1/4" OD, .17 ID	6.4 mm OD, 4.3 mm ID	NS2D120412	0.88 (22.4)	1.87 (47.5)
	1/8" ID	3.2 mm ID	NS2D160212	0.88 (22.4)	1.79 (45.5)
 PANEL MOUNT HOSE BARB	1/4" ID	6.4 mm ID	NS2D160412	0.88 (22.4)	2.05 (52.1)


## COUPLING INSERTS - Polypropylene

TERMINATION	TUBING/THREAD SIZE	METRIC EQ.	SHUTOFF	A	B
 IN-LINE PIPE THREAD	1/8" NPT		NS2D240212	0.64 (16.3)	1.27 (32.3)
 IN-LINE FERRULELESS POLYTUBE FITTING, PTF†	1/4" OD, .17 ID	6.4 mm OD, 4.3 mm ID	NS2D200412	0.64 (16.3)	1.39 (35.3)
 IN-LINE HOSE BARB	1/8" ID	3.2 mm ID	NS2D220212	0.64 (16.3)	1.32 (33.5)
	1/4" ID	6.4 mm ID	NS2D220412	0.64 (16.3)	1.52 (38.6)

## ACCESSORIES


DESCRIPTION	MATERIAL	PART NO.
PANEL MOUNT GASKET REPLACEMENT: FOR SEALING PANEL MOUNT BODIES LISTED ABOVE	Buna-N	1830300

## PRODUCT DIMENSIONS



## PANEL DIMENSIONS

	PANEL OPENING	PANEL THICKNESS MAX.-MIN.
COUPLING BODIES	see drawing	0.30-0.05



WARRANTY: All sales are subject to the Colder Products Company® limited express warranty set forth in the CPC catalog. Contact your local distributor or CPC Customer Service for warranty provisions.

Warning: Due to the wide variety of possible fluid media and operating conditions, unintended consequences may result from the use of this product, all of which are beyond the control of CPC. It is the user's responsibility to carefully determine and test for compatibility for use with their application. All such risks shall be assumed by the buyer.

COPYRIGHT © 2026 BY COLDER PRODUCTS COMPANY.

CPC, Colder Products Company, and Colder Products are registered trademarks with the United States Patent and Trademark Office.

For detailed trademark information, please visit: <https://www.cpcworldwide.com/Trademarks>