



Load feeder fuseless, Reversing duty 400 V AC, Size S00 9.00...12.5 A 24 V DC  
Spring-type terminal for 60 mm busbar systems Type of coordination 1, I<sub>q</sub> = 150 kA  
1 NC (contactor) Adapter length 200 mm

|                                                                                     |                               |
|-------------------------------------------------------------------------------------|-------------------------------|
| product brand name                                                                  | SIRIUS                        |
| product designation                                                                 | Reversing starter             |
| design of the product                                                               | for 60 mm busbars             |
| product type designation                                                            | 3RA22                         |
| manufacturer's article number                                                       |                               |
| • of the supplied contactor                                                         | <a href="#">3RT2017-2BB42</a> |
| • of the supplied circuit-breakers                                                  | <a href="#">3RV2011-1KA20</a> |
| • of the supplied RS assembly kit                                                   | <a href="#">8US1250-5AS10</a> |
| • of the supplied busbar adapter                                                    | <a href="#">8US1251-5DS11</a> |
| • of the supplied link module                                                       | <a href="#">3RA2911-2AA00</a> |
| • of the supplied wiring kit                                                        | <a href="#">3RA2913-2AA2</a>  |
| <b>General technical data</b>                                                       |                               |
| size of the circuit-breaker                                                         | S00                           |
| size of load feeder                                                                 | S00                           |
| power loss [W] for rated value of the current                                       |                               |
| • at AC in hot operating state per pole                                             | 3.6 W                         |
| • without load current share typical                                                | 4 W                           |
| insulation voltage with degree of pollution 3 at AC rated value                     | 690 V                         |
| surge voltage resistance rated value                                                | 6 kV                          |
| degree of protection NEMA rating                                                    | other                         |
| shock resistance according to IEC 60068-2-27                                        | 6g / 11 ms                    |
| mechanical service life (operating cycles) of contactor typical                     | 30 000 000                    |
| type of coordination                                                                | 1                             |
| reference code according to IEC 81346-2:2019                                        | Q                             |
| Substance Prohibitance (Date)                                                       | 10/01/2009                    |
| SVHC substance name                                                                 | Lead - 7439-92-1              |
| Weight                                                                              | 1.939 kg                      |
| <b>Ambient conditions</b>                                                           |                               |
| ambient temperature                                                                 |                               |
| • during operation                                                                  | -20 ... +60 °C                |
| • during storage                                                                    | -50 ... +80 °C                |
| • during transport                                                                  | -50 ... +80 °C                |
| temperature compensation                                                            | -20 ... +60 °C                |
| relative humidity during operation                                                  | 10 ... 95 %                   |
| <b>Main circuit</b>                                                                 |                               |
| number of poles for main current circuit                                            | 3                             |
| design of the switching contact                                                     | electromechanical             |
| adjustable current response value current of the current-dependent overload release | 9 ... 12.5 A                  |
| operating voltage                                                                   |                               |

|                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• rated value</li> <li>• at AC-3 rated value maximum</li> <li>• at AC-3e rated value maximum</li> </ul>                                                                                                                                                                                                                                                                        | 690 V<br>690 V<br>690 V                                                              |
| <b>operating frequency rated value</b>                                                                                                                                                                                                                                                                                                                                                                                | 50 ... 60 Hz                                                                         |
| <b>operational current</b>                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                      |
| <ul style="list-style-type: none"> <li>• at AC-3 at 400 V rated value</li> <li>• at AC-3e at 400 V rated value</li> </ul>                                                                                                                                                                                                                                                                                             | 12 A<br>12 A                                                                         |
| <b>operating power</b>                                                                                                                                                                                                                                                                                                                                                                                                |                                                                                      |
| <ul style="list-style-type: none"> <li>• at AC-3 <ul style="list-style-type: none"> <li>— at 400 V rated value</li> </ul> </li> <li>• at AC-3e <ul style="list-style-type: none"> <li>— at 400 V rated value</li> </ul> </li> </ul>                                                                                                                                                                                   | 5 500 W<br>5 500 W                                                                   |
| <b>Control circuit/ Control</b>                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                      |
| <b>type of voltage of the control supply voltage</b>                                                                                                                                                                                                                                                                                                                                                                  | DC                                                                                   |
| <b>control supply voltage at DC rated value</b>                                                                                                                                                                                                                                                                                                                                                                       | 24 V                                                                                 |
| <b>holding power of magnet coil at DC</b>                                                                                                                                                                                                                                                                                                                                                                             | 4 W                                                                                  |
| <b>Auxiliary circuit</b>                                                                                                                                                                                                                                                                                                                                                                                              |                                                                                      |
| <b>product extension auxiliary switch</b>                                                                                                                                                                                                                                                                                                                                                                             | Yes                                                                                  |
| <b>Protective and monitoring functions</b>                                                                                                                                                                                                                                                                                                                                                                            |                                                                                      |
| <b>trip class</b>                                                                                                                                                                                                                                                                                                                                                                                                     | CLASS 10                                                                             |
| <b>design of the overload release</b>                                                                                                                                                                                                                                                                                                                                                                                 | thermal (bimetallic)                                                                 |
| <b>response value current of instantaneous short-circuit trip unit</b>                                                                                                                                                                                                                                                                                                                                                | 163 A                                                                                |
| <b>UL/CSA ratings</b>                                                                                                                                                                                                                                                                                                                                                                                                 |                                                                                      |
| <b>full-load current (FLA) for 3-phase AC motor</b>                                                                                                                                                                                                                                                                                                                                                                   |                                                                                      |
| <ul style="list-style-type: none"> <li>• at 480 V rated value</li> <li>• at 600 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                              | 11 A<br>11 A                                                                         |
| <b>yielded mechanical performance [hp]</b>                                                                                                                                                                                                                                                                                                                                                                            |                                                                                      |
| <ul style="list-style-type: none"> <li>• for single-phase AC motor <ul style="list-style-type: none"> <li>— at 110/120 V rated value</li> <li>— at 230 V rated value</li> </ul> </li> <li>• for 3-phase AC motor <ul style="list-style-type: none"> <li>— at 200/208 V rated value</li> <li>— at 220/230 V rated value</li> <li>— at 460/480 V rated value</li> <li>— at 575/600 V rated value</li> </ul> </li> </ul> | 0.5 hp<br>2 hp<br>3 hp<br>3 hp<br>7.5 hp<br>10 hp                                    |
| <b>Short-circuit protection</b>                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                      |
| <b>product function short circuit protection</b>                                                                                                                                                                                                                                                                                                                                                                      | Yes                                                                                  |
| <b>design of the short-circuit trip</b>                                                                                                                                                                                                                                                                                                                                                                               | magnetic                                                                             |
| <b>conditional short-circuit current (I<sub>q</sub>)</b>                                                                                                                                                                                                                                                                                                                                                              |                                                                                      |
| <ul style="list-style-type: none"> <li>• at 400 V according to IEC 60947-4-1 rated value</li> </ul>                                                                                                                                                                                                                                                                                                                   | 150 000 A                                                                            |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                                                                                                                                                                                                             |                                                                                      |
| <b>mounting position</b>                                                                                                                                                                                                                                                                                                                                                                                              | vertical                                                                             |
| <b>fastening method</b>                                                                                                                                                                                                                                                                                                                                                                                               | for snapping onto 60 mm busbar systems                                               |
| <b>height</b>                                                                                                                                                                                                                                                                                                                                                                                                         | 230 mm                                                                               |
| <b>width</b>                                                                                                                                                                                                                                                                                                                                                                                                          | 90 mm                                                                                |
| <b>depth</b>                                                                                                                                                                                                                                                                                                                                                                                                          | 155 mm                                                                               |
| <b>required spacing</b>                                                                                                                                                                                                                                                                                                                                                                                               |                                                                                      |
| <ul style="list-style-type: none"> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— backwards</li> <li>— upwards</li> <li>— at the side</li> <li>— downwards</li> </ul> </li> <li>• for live parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— backwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> </ul>                  | 32 mm<br>0 mm<br>50 mm<br>10 mm<br>10 mm<br>32 mm<br>0 mm<br>50 mm<br>10 mm<br>10 mm |
| <b>Connections/ Terminals</b>                                                                                                                                                                                                                                                                                                                                                                                         |                                                                                      |

|                                                                                                                           |                                                    |
|---------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------|
| <b>type of electrical connection</b>                                                                                      |                                                    |
| <ul style="list-style-type: none"> <li>• for main current circuit</li> <li>• for auxiliary and control circuit</li> </ul> | spring-loaded terminals<br>spring-loaded terminals |
| <b>Safety related data</b>                                                                                                |                                                    |
| product function suitable for safety function                                                                             | Yes                                                |
| <b>Electrical Safety</b>                                                                                                  |                                                    |
| <b>touch protection on the front according to IEC 60529</b>                                                               | finger-safe, for vertical contact from the front   |
| <b>Communication/ Protocol</b>                                                                                            |                                                    |
| <b>protocol is supported</b>                                                                                              |                                                    |
| <ul style="list-style-type: none"> <li>• PROFINET IO protocol</li> <li>• PROFIsafe protocol</li> </ul>                    | No<br>No                                           |
| protocol is supported AS-Interface protocol                                                                               | No                                                 |

#### Approvals Certificates

|                          |                                |                   |
|--------------------------|--------------------------------|-------------------|
| General Product Approval | For use in hazardous locations | Test Certificates |
|--------------------------|--------------------------------|-------------------|



[Type Test Certificates/Test Report](#)

|                   |                      |
|-------------------|----------------------|
| Test Certificates | Maritime application |
|-------------------|----------------------|

[Special Test Certificate](#)



|                      |       |                 |             |
|----------------------|-------|-----------------|-------------|
| Maritime application | other | Dangerous goods | Environment |
|----------------------|-------|-----------------|-------------|



[Confirmation](#)

[Transport Information](#)

[Environmental Confirmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-1KS17-2BB4>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-1KS17-2BB4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1KS17-2BB4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)



[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RA2210-1KS17-2BB4&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-1KS17-2BB4&lang=en)

Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1KS17-2BB4/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-1KS17-2BB4&objecttype=14&gridview=view1>



last modified:

4/1/2025 