



Product data sheet

Power tools for trade & industry

Cordless Drill/Driver

PRO GSR 12V-32



Bosch Professional's first 12V drill driver with Advanced KickBack Control

The most important data

Torque (soft/hard/max.)	21/32/- Nm
No-load speed (1st gear / 2nd gear)	0 – 475 / 0 – 1,800 rpm
Battery voltage	12.0 V

Part Number 0 601 9N7 001

Technical data

Technical data

Torque (soft/hard/max.)	21/32/- Nm
No-load speed (1st gear / 2nd gear)	0 – 475 / 0 – 1,800 rpm
Battery type	Lithium-Ion
Chuck capacity, min./max.	0.8 / 10 mm
Battery voltage	12.0 V
Weight excl. battery	0.7 kg
Torque settings	21
Packaging dimensions (width x length x height)	360 x 444 x 117 mm
Chuck type	Keyless
BITURBO	No
Chuck with click	+
Belt clip option	+
KickBack Control	+
Work light	+
Tool design	T-Handle
Tool fitting/shank	Clamped

Noise/vibration information

Drilling in metal

Vibration emission value ah	1.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High user protection thanks to Advanced KickBack Control, which minimises the risk of injury
- Precise and convenient working even in tight spaces and hard-to-reach spots due to highly compact design
- Work longer with less fatigue thanks to lightweight tool weighing only 0.7 kg

**HEAVY
DUTY****32/21
Nm****0-475/
1800
min⁻¹/rpm****KICKBACK
CONTROL****BRUSHLESS
MOTOR****142 mm****PROFESSIONAL
12V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

