

YASMEEN-50-WW

~60° wide beam

SPECIFICATION:

Dimensions	Ø 49.9
Height	28.1 mm
Fastening	socket
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
YASMEEN-50-WW	Single lens	PMMA	clear		
YASMEEN-50-HLD2-C	Holder C	PC	black		
YASMEEN-50-HLD2-B	Holder B	PC	black		
YASMEEN-50-HLD2-C-WHT	Holder C	PC	white		
YASMEEN-50-HLD2-B-WHT	Holder B	PC	white		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C17237_YASMEEN-50-WW	252	112	28	7.9
Assembly				
CP18747_YASMEEN-50-WW-B2-WHT	252	112	28	9.3
CP18740_YASMEEN-50-WW-C2-WHT	252	112	28	9.1
CP18733_YASMEEN-50-WW-B2	252	112	28	9.3
CP18726_YASMEEN-50-WW-C2	252	112	28	9.1





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED V10 Gen 8-9
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 55.0° / 77.0°
Efficiency 82 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files





LED V11 HD Gen 8
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 54.0° / 76.0°
Efficiency 83 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 Bender Wirth: 633d Hekla



Light distribution files



LED V11 HD Gen 8
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 54.0° / 78.0°
Efficiency 92 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 Bender Wirth: 633d Hekla





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V13 Gen 8-9
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 50.0° / 77.0°
 Efficiency 79 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files





LED V4 HD Gen 7
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 76.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V6 HD Gen 7
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V6 HD Gen 7
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 55.0° / 75.0°
Efficiency 83 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files





LED V8 Gen 8-9
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 55.0° / 76.0°
Efficiency 83 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED VERO10
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 54.0° / 76.0°
Efficiency 82 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15616_HEKLA-SOCKET-F





Light distribution files

OPTICAL RESULTS (MEASURED):





LED VERO10
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 55.0° / 78.0°
Efficiency 90 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15616_HEKLA-SOCKET-F



Light distribution files





LED Vesta DTW 13mm (21W)
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 51.0° / 80.0°
Efficiency 90 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 Bender Wirth: 632b Hekla XL



Light distribution files



LED Vesta DTW 13mm (21W)
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 51.0° / 78.0°
Efficiency 79 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 Bender Wirth: 632b Hekla XL





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Vesta DTW 15mm (33W)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 49.0° / 80.0°
 Efficiency 89 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 632b Hekla XL



Light distribution files





LED Vesta DTW 15mm (33W)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 49.0° / 78.0°
 Efficiency 79 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 632b Hekla XL



Light distribution files



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 652b Hekla





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 55.0° / 76.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 652b Hekla



Light distribution files





LED Vesta RGBW 10mm CSP
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 78.0°
 Efficiency 70 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 28
 Light colour/type RGBW
 Required components:
 C19950_HEKLA-SOCKET-RZ



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 78.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU02x (LES10)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 76.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN



LED CLU700/701/702/703
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 55.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN


LED CLU7A2/7A3
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 76.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN



LED CLU7A2/7A3
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 55.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU7B2
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 76.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU7B2
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 74.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files





LED CMA1516
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 78.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D



Light distribution files



LED CMA1516
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 76.0°
 Efficiency 83 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D





Light distribution files

OPTICAL RESULTS (MEASURED):




LED CMT14xx
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 54.0° / 76.0°
Efficiency 83 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files





LED CMT14xx
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 54.0° / 78.0°
Efficiency 91 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files



LED CMU10xx
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 48.0° / 72.0°
Efficiency 81 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CXA/B 13xx
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J



Light distribution files





LED CXA/B 13xx
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 55.0° / 74.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J



Light distribution files



LED CXA/B 15xx
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CXA/B 15xx
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 78.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D



Light distribution files





LED LEDIM/C6
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 57.0° / 78.0°
 Efficiency 83 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED LUXEON CoB 1202/1203
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB 1202/1203
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 77.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files





LED LUXEON CoB 1204HD
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 53.0° / 75.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files



LED LUXEON CoB 1204HD
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB M02/M03
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D



Light distribution files





LED LUXEON CoB M02/M03
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D



Light distribution files



LED LUXEON CoB S01
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 55.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB S01
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J



Light distribution files





LED CTM-14 (Tunable White) Gen2
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 50.0° / 76.0°
 Efficiency 79 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 442 Typ L8



Light distribution files



LED CXM-3
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 76.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):





LED CXM-3
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 55.0° / 75.0°
Efficiency 84 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files





LED CXM-4
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 55.0° / 75.0°
Efficiency 84 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files



LED CXM-4
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 55.0° / 77.0°
Efficiency 92 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):





LED COB L-Type (LES 9)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 78.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files




LED COB S-Type (LES 7)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 90 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15848_HEKLA-SOCKET-G



Light distribution files



LED Fortimo SLM C TW L06A 1313 G7N
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 508 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS



LED Fortimo SLM C TW L09A 1919 G7N
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 82 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 501 Typ L8



Light distribution files

PHILIPS



LED Fortimo SLM L09 CoB
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 77.0°
 Efficiency 92 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files

PHILIPS

LED Fortimo SLM L09 CoB
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 78.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

SAMSUNG



LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 76.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED MJT COB LES 6
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 55.0° / 75.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):





LED MJT COB LES 6
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 55.0° / 77.0°
 Efficiency 93 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files





LED MJT COB LES 9.8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 76.0°
 Efficiency 83 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED MJT COB LES 9.8
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 54.0° / 78.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V3 HD Gen 8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 76.0°
 Efficiency 89 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V3 HD Gen 8 FC
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 64.0° / 77.0°
 Efficiency 88 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files




LED V4 HD Gen 8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 76.0°
 Efficiency 89 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V6 Gen 8-9
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 78.0°
 Efficiency 87 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files




LED V6 HD Gen 8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 78.0°
 Efficiency 87 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files



LED V9 HD Gen 8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 79.0°
 Efficiency 85 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED Vero SE 13
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 44.0° / 69.0°
 Efficiency 77 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files




LED VERO13
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 82.0°
 Efficiency 80 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files



LED Vesta DTW 6mm
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 78.0°
 Efficiency 87 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 652b Hekla

OPTICAL RESULTS (SIMULATED):




LED Vesta SE 13mm TW
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 49.0° / 74.0°
 Efficiency 77 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files



LED Vesta TW 13mm (18W) DP
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 53.0° / 76.0°
 Efficiency 81 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 492 Typ L8



LED Vesta TW 15mm DP
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 50.0° / 78.0°
 Efficiency 78 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 482 Typ L8

OPTICAL RESULTS (SIMULATED):



LED Vesta TW 9mm (9W) DP
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 64.0° / 83.0°
 Efficiency 78 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 489 Typ L8

CITIZEN


LED CLU02Q Type-F
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 82.0°
 Efficiency 80 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP18747_YASMEEN-50-WW-B2-WHT
 FWHM / FWTM 60.0° / 80.0°
 Efficiency 92 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1020

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU02x (LES10)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1020

CITIZEN

LED CLU02x (LES10)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 60.0° / 80.0°
 Efficiency 91 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU02x (LES10)
 Ordering code C17237_YASMEEN-50-WW
 FWHM / FWTM 62.0° / 80.0°
 Efficiency 96 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

CITIZEN


LED CLU02x (LES10)
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 60.0° / 80.0°
 Efficiency 92 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code C17237_YASMEEN-50-WW
 FWHM / FWTM 64.0° / 78.0°
 Efficiency 96 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU700/701/702/703
 Ordering code CP18740_YASMEEN-50-WW-C2-WHT
 FWHM / FWTM 62.0° / 78.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN


LED CLU700/701/702/703
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 77.0°
 Efficiency 89 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU712/713
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU713 Type-F
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 64.0° / 82.0°
 Efficiency 80 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN


LED CLU723 Type-F
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 61.0° / 82.0°
 Efficiency 78 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED CMB1818-25
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 57.0° / 80.0°
 Efficiency 81 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 637a Hekla

OPTICAL RESULTS (SIMULATED):




LED CMU10xx
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files




LED CXA/B 13xx
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 77.0°
 Efficiency 88 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J



Light distribution files



LED LUXEON CX Plus CoB L08 (Gen2)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 52.0° / 79.0°
 Efficiency 79 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 637a Hekla

OPTICAL RESULTS (SIMULATED):




LED LUXEON 7070
FWHM / FWTM 60.0° / 76.0°
Efficiency 96 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON CoB 1202/1203
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 60.0° / 78.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F15858_HEKLA-SOCKET-H



Light distribution files



LED LUXEON CoB 1202HD
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 62.0° / 78.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F15848_HEKLA-SOCKET-G



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED LUXEON CoB 1204/1205
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 56.0° / 79.0°
 Efficiency 81 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Bender Wirth: 632a Hekla XL

Light distribution files



LED LUXEON CoB 1205HD
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 58.0° / 79.0°
 Efficiency 84 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H


Light distribution files



LED LUXEON CoB 1208
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 52.0° / 78.0°
 Efficiency 80 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 632a Hekla XL


Light distribution files



OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB - HD S01H4
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 64.0° / 78.0°
 Efficiency 86 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB - HD S02H6
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 63.0° / 78.0°
 Efficiency 84 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB - HD S04H9
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 62.0° / 80.0°
 Efficiency 81 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 56.0° / 78.0°
 Efficiency 82 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15254_HEKLA-SOCKET-B



Light distribution files




LED LUXEON CX Plus CoB M02 / M03 (Gen2)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15256_HEKLA-SOCKET-D



Light distribution files



LED LUXEON CX Plus CoB S01 (Gen2)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 77.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15956_HEKLA-SOCKET-J




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CHM-9 XH (19x19)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files



LED CTM-6 (Tunable White) Gen2
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 78.0°
 Efficiency 87 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8



LED CTM-9 (Tunable White) Gen2
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 59.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files


Bender Wirth: 495 Typ L8

OPTICAL RESULTS (SIMULATED):



LED CxM-6 (13.5x13.5)
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 60.0° / 76.0°
 Efficiency 89 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


BJB: 47.360.1020



Light distribution files



LED COB L-Type (LES 11)
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 58.0° / 80.0°
 Efficiency 83 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H




Light distribution files



LED COB S-Type (LES 6)
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 64.0° / 78.0°
 Efficiency 85 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Bayonet35L



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED COB S-Type (LES 7)
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 64.0° / 78.0°
 Efficiency 84 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Bayonet35L


Light distribution files



LED COB T-Type
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 64.0° / 78.0°
 Efficiency 85 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Bayonet35L


Light distribution files



LED NJCWL024Z-V1MT: COB L-Type Tunable White
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 76.0°
 Efficiency 87 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K

Bender Wirth: 497 Typ L8 HV


Light distribution files



OPTICAL RESULTS (SIMULATED):



LED NJNWS012Z-V1MT: COB S-Type Tunable White
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 62.0° / 76.0°
 Efficiency 88 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8 HV



LED NVCWJ024Z-V1MT: COB J-Type Tunable White
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 63.0° / 84.0°
 Efficiency 81 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 498 Typ L8 HV



LED NVCWJ024Z-V1MT: COB J-Type Tunable White
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 58.0° / 78.0°
 Efficiency 84 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 498 Typ L8 HV

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED Soleriq S15
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 56.0° / 84.0°
Efficiency 89 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I



Light distribution files

PHILIPS


LED Fortimo SLM L13 CoB
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 48.0° / 74.0°
Efficiency 87 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

PHILIPS

LED Fortimo SLM L15 CoB
Ordering code CP18740_YASMEEN-50-WW-C2-WHT
FWHM / FWTM 46.0° / 75.0°
Efficiency 86 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC010C G2
Ordering code CP18733_YASMEEN-50-WW-B2
FWHM / FWTM 60.0° / 76.0°
Efficiency 89 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

BJB: 47.360.1020




Light distribution files

SAMSUNG

LED LC010T (Tunable White)
Ordering code CP18726_YASMEEN-50-WW-C2
FWHM / FWTM 60.0° / 78.0°
Efficiency 87 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type Tunable White
Required components:
C16142_HEKLA-SOCKET-K

Bender Wirth: 501 Typ L8




Light distribution files

SAMSUNG

LED LC016D / LC019D / LC026D / LC033D
Ordering code CP18733_YASMEEN-50-WW-B2
FWHM / FWTM 53.0° / 80.0°
Efficiency 77 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

BJB: 47.360.1010



Light distribution files


OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC020C G2
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.360.1010

Light distribution files




SAMSUNG

LED LC030C/040C G2
 Ordering code CP18733_YASMEEN-50-WW-B2
 FWHM / FWTM 58.0° / 78.0°
 Efficiency 82 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


BJB: 47.360.1010

Light distribution files



LED MJT COB LES 14.5
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 54.0° / 80.0°
 Efficiency 80 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I


Light distribution files



OPTICAL RESULTS (SIMULATED):

TRIDONIC


LED SLE 09mm 1200lm xxx R ADV8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

TRIDONIC


LED SLE 13mm 3000lm xxx R ADV8
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 58.0° / 82.0°
 Efficiency 80 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

TRIDONIC

LED SLE G7 LES13
 Ordering code CP18726_YASMEEN-50-WW-C2
 FWHM / FWTM 56.0° / 80.0°
 Efficiency 81 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)