

Connecting cable NEBU-M12G5-E-5-Q8N-LE5

Part number: 8078303

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Conforms to standard	EN 61076-2-101 IEC 61010-1
Cable designation	Without inscription label holder
Frequency of connection	100
Product weight	422 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, used connections/cores	5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00995384
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connector system	Open end
Electrical connection 2, number of connections/cores	5
Electrical connection 2, used connections/cores	5
Operational voltage range DC	0 V ... 60 V
Operational voltage range AC	0 V ... 60 V
Current rating at 40° C	4 A
Immunity to surge	1.5 kV
Cable length	5 m
Cable characteristic	Suitable for energy chains
Test conditions cable	Bending strength: to Festo standard Test conditions on request Energy chain: > 5 million cycles, bending radius 75 mm
Bending radius, fixed cable	21 mm
Bending radius, moving cable	71 mm
Cable diameter	7 mm
Cable diameter tolerance	± 0.1 mm
Cable structure	5 x 1 mm ²
Nominal cross section conductor	1 mm ²
Wire ends	Stripped Cut off bluntly

Feature	Value
Degree of protection	IP65 IP68 IP69K
Note on degree of protection	In mounted state
Special characteristics	Oil-resistant
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with moving cable	-5 °C ... 80 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant Free of halogen Free of phosphoric acid ester
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Material housing	TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Brass, nickel-plated
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulating sheath	PP