




Switches > Slide Switches



Contact Current Rating: **.3 A**

Configuration (Pole-Throw): **Double Pole - Double Throw**

Product Orientation: **Vertical**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Features

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Number of Positions	2
Operating Function	On On

Electrical Characteristics

Contact Current Rating	.3 A
Operating Voltage	28 VDC

Body Features

Actuator Orientation	Top
Actuator Travel	2.79 mm[.11 in]
Product Orientation	Vertical
Actuator Profile	Extended
Actuator Material	Nylon
Actuator Color	Natural



Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver

Termination Features

Termination Post & Tail Length	4.06 mm[.16 in]
Termination Method to PCB	Through Hole - Solder

Dimensions

Product Width	7.37 mm[.29 in]
Product Length	10.16 mm[.4 in]
Actuator Length	2.79 mm[.11 in]

Operation/Application

Assembly Process Feature	Auto-Insert Packaging
--------------------------	-----------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Other

Grade	Telecom
-------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-1825010-0 ASE62RG04=6PDT AUTOSLIDE	 TE Part # 4-1825010-4 ASE62S04=6PDT AUTOSLIDE	 TE Part # 1-1825010-7 ASE42GL04=4PDT AUTOSLIDE	 TE Part # 2-1825010-7 ASE43R04=4P3T AUTOSLIDE
 TE Part # 2-1825010-5 ASE4304=4P3T AUTOSLIDE	 TE Part # 1-1825010-4 ASE42G04=4PDT AUTOSLIDE	 TE Part # 1825010-7 ASE22GS04=DPDT AUTOSLIDE	 TE Part # 1-1825010-6 ASE42RG04=4PDT AUTOSLIDE
 TE Part # 1825010-4 ASE22RG04=DPDT AUTOSLIDE	 TE Part # 1825010-6 ASE22L04=DPDT AUTOSLIDE	 TE Part # 1825010-5 ASE22GL04=DPDT AUTOSLIDE	 TE Part # 1-1825010-3 ASE4204=4PDT AUTOSLIDE
 TE Part # 1-1437581-4 ASE42=4PDT AUTO-SLIDE	 TE Part # 1-1825010-8 ASE42L04=4PDT AUTOSLIDE	 TE Part # 3-1825010-6 ASE43RS04=4P3T AUTOSLIDE	 TE Part # 1825010-2 ASE22G04=DPDT AUTOSLIDE




TE Part # 1437581-4
ASE22G=DPDT AUTO-SLIDE



TE Part # 3-1825010-7
ASE6204=6PDT AUTOSLIDE




TE Part # 2-1437581-2
ASE42RL=4 POLE L BEND SLIDE SW




TE Part # 1437581-2
ASE22=DPDT AUTO-SLIDE SWITCH

Also in the Series | [Alcoswitch ASE/F](#)



[Slide Switches\(46\)](#)

Customers Also Bought



TE Part #1676428-1
RN 0805 75R 0.1% 10PPM CUT LENGTH




TE Part #3-640429-4
04P MTA156 CONN ASSY 24AWG WHT



TE Part #2176411-4
1/2W SM M/OX 5% 15K



TE Part #826469-6
2X6P MOD II SHROUDED HEADER, ST



TE Part #3-640426-5
05P MTA156 CONN ASSY 18AWG ORA



TE Part #350428-1
02P UMNL PIN HDR ASSY NATL



TE Part #7-2176367-2
RQ 0603 25K5 0.1% 10PPM 1K RL



TE Part #1-2176056-9
RLP73N 2B R056 5% 5K RL



TE Part #1625892-5
3W SM M/OX 5% R47



TE Part #5-2213767-5
AV19 DPM 3A MOVE RING LED GREEN 24V



Documents

Product Drawings

ASE2204=DPDT AUTOSLIDE

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825010-1_D1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1825010-1_D1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1825010-1_D1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English