


64 12 115 ESD

Electronics End Cutting Nippers ESD



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- With two-colour dual component grips, black/grey
- High-grade special tool steel, forged, multi stage oil-hardened
 - Style:End Cutter, with small bevel



ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Article No.	64 12 115 ESD
EAN	4003773017806
Head	mirror polished
Handles	with multi-component grips
Style	1
Cutting capacities medium hard wire (diameter) Ø mm	0,8
Cutting capacities hard wire (diameter) Ø mm	
Cutting capacities soft wire (diameter) Ø mm	1,4
B mm	6,0
D mm	7,0
C mm	16,0
A mm	11,0
Length mm	115
Net weight g	94

technical change and errors excepted

