


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	WEIGHT lbs/100pcs (g)
	MIN in (mm)	MAX in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	90 (400.3)	EXTRA HEAVY	1.3 (590)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	90 (400.3)	EXTRA HEAVY	2.5 (1134)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	90 (400.3)	EXTRA HEAVY	2.8 (1270)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	90 (400.3)	EXTRA HEAVY	3.8 (1724)

* SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR

						TITLE PAN-TY RELEASABLE LASHING TIES - POLYPROPYLENE CUSTOMER DRAWING						
						ITEM REVISION NAME W10001BH/07						
						DATASET FILE NAME W10001BH_DC/07						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.5] .xxx ± .010 [.25] .xx ± .02 [.5] ANGLES ±						
						DRAWING NUMBER: SS-15129			MATERIAL: POLYPROPYLENE			
7 11.18.14 BDK MPH JADE UPDATED TITLE BORDER SS-15129						THIRD ANGLE PROJECTION			DRAWING NUMBER: SS-15129			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							DWR	7-15-77	HVP	NONE		A

2

1

D110100DA/16