

## Marker for terminal blocks - ZB 5,08,LGS:U-N - 0809845

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Marker for terminal blocks, Strip, white, labeled, Printed horizontally: U, V, W, N, GND, U, V, W, N, GND, Mounting type: Snap into tall marker groove, for terminal block width: 5.08 mm, Lettering field: 10.5 x 5.15 mm

### Why buy this product

- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unlabeled marking strips can be custom-labeled with a plotter or by hand



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 591809
Weight per Piece (excluding packing)	1.03 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width (a)	5 mm
-----------	------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Note	10 identically marked strips make up one packing unit (PU).
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2

# Marker for terminal blocks - ZB 5,08,LGS:U-N - 0809845

## Technical data

### General

Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing direction	Printed horizontally
Printing	U, V, W, N, GND, U, V, W, N, GND
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Marking mounting type	Snap into tall marker groove

## Classifications

### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410