

Endress+Hauser Vibronic level switch FTM20-AA28A

Compact and universal single rod probe for point level detection in bulk solids



Picture for reference only. Product appearance may vary based on configuration

The Soliphant FTM20 is a point level switch for applications with fine-grained or coarse-grained, non-fluidized bulk solids. The various designs means the device has a wide range of applications. Certificates are also available for use in dust and hazardous areas.

- Measurement is unaffected by conductivity, build-up, turbulence, flows or air bubbles
- Simple and fast commissioning, no calibration required
- No mechanically moved parts, free of maintenance

Configuration of FTM20-AA28A:

Approval:	A	Non-hazardous area
Process Connection:	A	Thread EN10226 R1, 316L
Electronics; Output:	2	FEM22; 3-wire PNP 10-45VDC
Housing; Cable Entry:	8	F18 Alu IP66/67 NEMA4x; M12 plug
Additional Option:	A	Basic version

Alternative part number: FTM20-AA28A