


stepper motor EMMS-ST-87-M-SB-G2

Part number: 1370488

☆ Core product range

Without gear unit/with brake.

FESTO



Data sheet

Feature	Value
Ambient temperature	-10 ... 50 °C
Storage temperature	-20 ... 70 °C
Relative air humidity	0 - 85 %
Conforms to standard	IEC 60034
Insulation protection class	B
Thermal class according to EN 60034-1	B
Rating class according to EN 60034-1	S1
Protection class	IP54
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	1 - Low corrosion stress
CE mark (see declaration of conformity)	to EU directive for EMC
Authorisation	RCM Mark c UL us - Recognized (OL)
Nominal operating voltage DC	48 V
Motor holding torque	5.9 Nm
Max. speed	550 1/min
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5 %
Nominal motor current	9.5 A
Voltage constant, phase	68.6 mVmin
Winding resistance phase	0.23 Ohm
Winding inductance phase	2.6 mH
Mass moment of inertia of rotor	1.9 kgcm ²
Overall mass moment of inertia at power take-off	1.97 kgcm ²
Product weight	3,450 g
Permissible axial shaft load	65 N
Permissible radial shaft load	200 N
Brake holding torque	2 Nm
Operating voltage DC for brake	24 V
Power consumption, brake	11 W
Mass moment of inertia of brake	0.07 kgcm ²