

FIRETRACE[®] Ltd

Automatic Fire Extinguisher Systems

Telephone: 01473 744090 Fax: 01473 744901 Email: Firetrace@aol.com

RS stock No. 433-7390

FIRETRACE LIMITED

SYSTEM SPECIFICATION SHEET No. 201DP

2 Kg Direct low pressure / Dry Powder with one 4000 mm sealed detection tube.

Firetrace Ltd

Part number : FS2/DLP/P/40

Canister type FT130 : Aluminium 2 Kg can.
Internal volume : 2218 ml
Thread size : M30 x 1.5
Colour red : RAL 3000
Pressure : 10 Bar OFN

Valve Type FT101 : Direct low pressure

Detection tube FT115 : Refer to data sheet.

Pressure Switch FT123 : Refer to data sheet.

Maintenance requirements : System contents gauge
Should be checked regularly

Discharge test required every five years in accordance with BS 5306.

Firetrace Ltd

Registered Office: Unit 22 • Knightsdale Road • Ipswich • Suffolk • IP1 4JJ
Directors: D. L. Melton • C. S. Melton • A. J. Melton Reg. UK No. 1388268