

FEATURES

- Flexible and durable cable with PVC insulation and sheath
- Fully moulded IEC C13 connector for strength and durability
- Reliable integrated strain relief for connection support and protection
- Untermated for flexibility and convenience when installing appliances

RS PRO 2m Power Cable, C13, IEC to Untermated, 10 A, 250 V

RS Stock No.: 744-0929



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro a high quality and durable power cable assembly or power cord for connecting an appliance to a mains power supply. This power cord is terminated on one end with an IEC C13 type connector that connects to the appliance. The other end of this power lead is unterminated and can be terminated to a plug when convenient. The power lead features an integrated strain relief that provides additional protection and support to the connector and prevents damage caused by excessive bending

General Specifications

Connector A	C13, IEC
Connector B	Unterminated
Sheath Colour	Black
Connector A Type	IEC
Mains Plug Type	Unterminated Cable
Mains Socket Type	IEC 60320 C13
Connector B Type	C14
Fire Behaviour	Low Smoke Zero Halogen (LSHZ)
Outer Sheath Material	PVC
Connector A Angle	Straight
Connector B Angle	Right Angle
Connector A Gender	Female
Connector B Gender	Male
Terminals	Brass
Conductor	3 Wire
Applications	DIY and home improvements Maintenance work Household entertainment (TVs, satellite boxes, routers etc.) Industrial machines and equipment Office desks (Monitors, computers, phones) Any electrical device needed to be powered by the mains, Cassette recorders, Battery/mains operated radios, Battery chargers, Laptop computer power supplies, Video game consoles

Electrical Specifications

Current Rating	10A
Voltage Rating	250V
Insulation Resistance	>10MΩ
Cable Retention	0.5mm ² -1mm ² >30N 1.25mm ² -1.5mm ² >60N
Electrical Strength	2.5kV 50Hz
Safety Test	4.4kV 50Hz
Capacitance	95.08pF/m
Inductance	0.43μH/m

Mechanical Specifications

Length	2m
Cross Sectional Area	7mm
Weight	175g
Withdrawal Force	10N-50N
Gauge	1.5mm ²
Copper Wire Stranding	48 Strands of 0.202mm ²

Operation Environment Specifications

Maximum Pin Temperature	65°C
--------------------------------	------

Approvals

Compliance/Certifications	CE / UR / cUR
Standards Met	GOST, IMQ, SEMKO, SEV, VDE

