



Connectors > Rectangular Connectors > Standard Rectangular Connectors > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Housing**
Connector System: **Wire-to-Board**
UL Flammability Rating: **UL 94V-0**
Number of Positions: **10**
Centerline (Pitch): **2 mm [.078 in]**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	10
Number of Rows	1

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features



Housing Material	66Nylon
Centerline (Pitch)	2 mm[.078 in]

Dimensions

Connector Width	5.1 mm[.2 in]
Connector Height	4 mm[.157 in]
Connector Length	22 mm[.866 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	UL
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-292161-0
CT P/HDR ASSY V 10P W/KINK NAT


Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)




PCB Headers & Receptacles(756)



Rectangular Connector Housings(72)




Rectangular Power Connectors(906)



Standard Rectangular Connectors(158)




Wire-to-Board Connector Assemblies & Housings(97)



Wire-to-Board Headers & Receptacles (756)

Customers Also Bought



TE Part #1-292161-0
CT P/HDR ASSY V 10P W/KINK NAT



TE Part #6609006-8
3EJS1=F8027



TE Part #1-175102-1
AMP CT CRIMP REC CONTACT



TE Part #1-329631-2
JAM NUT, PLATED



Documents

Product Drawings

CT. CRIMP REC HSG 10P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-175778-0_D1.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-175778-0_D1.3d_igs.zip

English

Customer View Model

ENG_CVM_1-175778-0_D1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Crimping AMP 2.0mm Pitch CT Receptacle Contact

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English