



Monitoring relay - voltage monitoring

Status: **Available** Data sheet created: **01.07.2025**

Item Number: 1341402 - Serie: Enya - EAN: 9008662005297



- ✓ Monitoring relay series ENYA
- ✓ Undervoltage monitoring 3-phase
- ✓ Measuring voltage = supply voltage
- ✓ Switching threshold fixed $U \times 0,85$
- ✓ Supply voltage 3x 400/230V AC
- ✓ 3 LED for phase indication
- ✓ Test - function
- ✓ Voltage monitoring in accordance with VDE 0108-100 & VDE 0100-718
- ✓ 2 changeover contacts
- ✓ width 35mm
- ✓ Installation type

Description

Undervoltage monitoring in 3- & 1-phase mains in accordance with VDE 0108-100 and VDE 0100-718 (each phase against the neutral wire) with fixed adjustable threshold and fixed adjustable hysteresis.


General information

Short description	Voltage monitoring 0.85, 3-phase against N, test function, 2 changeover contacts
Item Number	1341402
EAN	9008662005297
Main category	Monitoring Relays
Series	Enya
Type	E3YF400VT02 0.85
Design	Installation design
Supply	400V AC
Dimensions	35 x 87 x 65 mm

Functions and measurands

Amount of functions

1



Undervoltage monitoring (UNDER)

The output relay R switches into on-position (yellow LED illuminated), when the measuring voltage of all connected phases exceeds the threshold U_S by more than the fixed hysteresis. When the voltage of one of the connected phases (L1, L2 or L3) falls below the fixed threshold (green LED L1, L2 or L3 illuminated), the output relay R switches into off position again (yellow LED not illuminated).

Time ranges

Number Of Areas

1

Adjustment range

Time ranges

Tripping delay:

fixed, approx. 200ms

Indicators

Supply/time lapse 1

Green LED ON/OFF: Display of supply voltage

Supply/time lapse 2

Green LED L2 ON/OFF: Indicator for voltage L2-N

Supply/time lapse 3

Green LED L3 ON/OFF: Display for voltage L3-N

Relay state

Yellow LED ON/OFF: output relay position

Mechanical design

Housing material

made of self-extinguishing plastic

Housing - protection degree

IP40

Mounting

top hat rail TH 35 7,5-15 according to IEC 60715:2017 / EN 60715:2017

Terminals/connections

Touch-proof clamping yoke terminals according to DGUV 3 (Screwdriver PZ1 required)

Terminals - protection degree

IP20

Mounting position

any

Max. Tightening Torque

1 Nm

Terminal capacity

- 1 x 0.5 to 2.5mm² with/without ferrule
- 1 x 4mm² without wire end ferrule
- 2 x 0.5 to 1.5mm² with/without end sleeves
- 2 x 2.5mm² flexible without ferrules

Supply circuit

Supply

(= Measuring voltage)

Terminals/connections

N-L1-L2-L3

Supply voltage a.c.

3(N)-400/230V (VDE 0108)

Supply voltage tolerance a.c.

-30% ... +30% U_n

Rated frequency [Hz]

a.c. 48 ... 63 Hz

Rated consumption a.c.

1,2 W / 11 VA

Duty cycle

100 %

Recovery time

500 ms

Drop-out voltage

defined by measuring function (see measuring circuit)

Overvoltage category

III (IEC 60664-1)

Rated surge voltage

6 kV



Output circuit

Type	Relay
Contact 1	1 change over contact
Terminals 1	11-12-14
Contacts 2	1 change over contact
Terminals/connections 2	21-22-24
Rated voltage	250 V a.c.
Switching Capacity 1	1250VA (5A / 250V)
Fuse Protection	5 A quick
Mechanical life	15 x 10 ⁶ Switching cycles
Electrical life	100 x 10 ³ Switching cycles (1000VA)
Switching frequency	max. 6/min at 1000VA resistive load (in accordance with IEC 60947-5-1)
Rated surge voltage	6 kV
Overvoltage category	III (nach IEC 60664-1)

Measuring circuit

Measurand	Current - three phase
Measuring range	(=supply voltage)
Terminals/connections	N-L1-L2-L3
Overload capacity	determined by tolerance specified for supply voltage
Frequency - sinusoidal	48 ... 63 Hz
Switching threshold minimum	fixed 195,5V
Hysteresis	approx. 5%
Rated surge voltage	6 kV
Overvoltage category	III (IEC 60664-1)

Accuracy

Base accuracy	≤5 %
Repetition accuracy	≤2 %
Temperature influence	≤0.05 % / °C

Ambient conditions and general specifications

Ambient temperature IEC	-25 ... +55 °C
Storage temperature	-25 ... +70 °C
Transport temperature	-25 ... +70 °C
Relative humidity	15% ... 85% (in accordance with IEC 60721-3-3 class 3K3)
Pollution degree	2, pollution level can be increased by installation in suitable enclosures (according to IEC 60664-1)

Logistics

Minimum Quantity	1
Tariff Number	85364900
EAN	9008662005297
Country of Origin	AT
Product Weight (g)	106



Available declarations / conformities

EAC ✓

CE [Open document](#)

REACH [Open document](#)

WEEE [Open document](#)

TSCA [Open document](#)


RoHs [Open document](#)

CMRT [Open document](#)

CAD Files

STEP_E3_en.STEP [Download file](#)

Media & drawings



Tele Haase Steuergeräte Ges.m.b.H

Vorarlberger Allee 38

1230 Vienna

Austria

CALL US



+43 / 1 / 614 74 - 0

ONLINE SUPPORT



support@tele-haase.at

Changes and errors excepted