



**Part Number :** [1715653002](#)

**Product Description :** zQuad Small Form Factor Pluggable Plus (zQSFP+) Stacked Integrated 2-by-3 Connector and Cage with Elastomeric Gasket, Gold (Au) Over Nickel Plated, Up/Down Light Pipe

**Series Number :** 171565

**Status :** Active

**Product Category :** High-Speed I/O Connectors



---

## Documents & Resources

### Drawings

[1715653002 sd.pdf](#)

[PK-171565-0001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-171565-3001-001.zip](#)

[EE-171081-3000-001.pdf](#)

[SP-171081-3000-001.zip](#)

### Specifications

[AS-171565-0002-001.pdf](#)

[PS-171565-0001-001.pdf](#)

[TS-171565-0001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Contains Perfluorobutane sulfonic acid (PFBS) and its salts per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	High-Speed I/O Connectors
Series	171565
Description	zQuad Small Form Factor Pluggable Plus (zQSFP+) Stacked Integrated 2-by-3 Connector and Cage with Elastomeric Gasket, Gold (Au) Over Nickel Plated, Up/Down Light Pipe
Application	Board-to-Board, Module-to-Board, Wire-to-Board
Component Type	Receptacle
Product Name	zQSFP Plus,zQSFP+
Type	Pluggable
UPC	887191264363

### Agency

UL	E29179
----	--------

## Electrical

Current - Maximum per Contact	0.5A
Data Rate	28.0 Gbps
Grounding to Panel	Yes
Voltage - Maximum	30V AC (RMS)/DC

## Physical

Circuits (Loaded)	228
Circuits (maximum)	228
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	96.028/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	N/A
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	1.20mm
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	6

Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
QSFP+-to-QSFP+ Cable Assemblies	<u>111040</u>
QSFP Cable Assemblies	<u>74757</u>
QSFP+ Universal Loopback Adapters	<u>74763</u>

---

### Application Tooling

---

This document was generated on Nov 06, 2025