

### Product description

Preset for Ethernet/IP mode!

SCALANCE XB208 managed Layer 2 IE Switch 8x 10/100 Mbit/s RJ45 ports 1x console port, Diagnostics LEDs Redundant power supply temp. range 0 to +60 °C mounting onto standard rail; Default EtherNet/IP



<b>Product type designation</b>	<b>SCALANCE XB208</b>
<b>Transfer rate</b>	
Transfer rate	10 Mbit/s, 100 Mbit/s
<b>Interfaces / for communication / Integrated</b>	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	8; RJ45
<b>Interfaces / other</b>	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for operator console</li> </ul>	1
<ul style="list-style-type: none"> <li>for management purposes</li> </ul>	1
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	1
<ul style="list-style-type: none"> <li>for redundant voltage supply</li> </ul>	1
Type of electrical connection	
<ul style="list-style-type: none"> <li>for operator console</li> </ul>	RJ11
<ul style="list-style-type: none"> <li>for management purposes</li> </ul>	RJ45
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	6-pole terminal block
<b>Supply voltage, current consumption, power loss</b>	

Type of voltage / of the supply voltage	DC
Supply voltage	
• external	24 V
• external / minimum	19.2 V
• external / maximum	28.8 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.17 A

#### Ambient conditions

Ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP20

#### Design, dimensions and weights

Design	compact
Width	40 mm
Height	117 mm
Depth	109 mm
Net weight	0.25 kg
Material / of the enclosure	Plastic
Mounting type	
• 35 mm DIN rail mounting	Yes
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No

#### Product features, product functions, product components / general

Cascading in the case of a redundant ring / at reconfiguration time of <math>\leq 0.3\text{ s}</math>	50
Cascading in cases of star topology	any (depending only on signal propagation time)

#### Product functions / management, configuration, engineering

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• RMON	Yes
• Port mirroring	Yes

• multiport mirroring	No
• CoS	Yes
• with IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
Product function / switch-managed	Yes
Telegram length / for Ethernet / maximum	1522 byte
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

### Product functions / Diagnostics

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
• SysLog	Yes
• loopback diagnostics	Yes

### Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	No

### Product functions / DHCP

Product function	
------------------	--

- DHCP client

Yes

### Product functions / redundancy

Product function	
<ul style="list-style-type: none"> <li>• Ring redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul style="list-style-type: none"> <li>• media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure STP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure MSTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/operation in the PRP-network</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	No
<ul style="list-style-type: none"> <li>• Passive listening</li> </ul>	Yes

### Product functions / Security

Product function	
<ul style="list-style-type: none"> <li>• IEEE 802.1x (radius)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Broadcast/Multicast/Unicast Limiter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• broadcast blocking</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• SSH</li> </ul>	Yes

### Product functions / time

Product function	
<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes

### Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> <li>• for FM</li> </ul>	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> <li>• for hazardous zone</li> </ul>	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-1

<ul style="list-style-type: none"> <li>• for hazardous zone / from CSA and UL</li> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4 EN 61000-6-4 (Class A) EN 61000-6-2
Security for industrial automation and control systems / acc. to IEC 62443-4-2:2019	Yes

Standards, specifications, approvals / CE	
Certificate of suitability / CE marking	Yes

Standards, specifications, approvals / other	
Certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> <li>• C-Tick</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Railway application in accordance with EN 50155</li> </ul>	No
<ul style="list-style-type: none"> <li>• Railway application in accordance with EN 50124-1</li> </ul>	No
<ul style="list-style-type: none"> <li>• KC approval</li> </ul>	Yes

Further information / Internet-Links	
Internet-Link	
<ul style="list-style-type: none"> <li>• to website: Selector SIMATIC NET SELECTION TOOL</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
<ul style="list-style-type: none"> <li>• to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>• to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>• to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
<ul style="list-style-type: none"> <li>• to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>• to website: CAx Download Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>• to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

Security information	
Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a>. (V3.4)</p>

last modified:

05/13/2020