




LED R7s Slim 12X118 7.5W (51W) 660lm 830

Article number 80100040401

BAI LED R7s Slim 12x118mm 9W 3000K Clear 660lm (51W) 230V-240V 360° Linear LED-lamp Open luminaire is recommended

These LED R7s lamps with ultra-thin housing and all-round light are ideal as a replacement for the two-pinched halogen lamps. Originally this type of lamp is used in construction lamps, but they are also increasingly used for general lighting in homes or catering establishments. Ambient temperature range: -20°C to +45°C. An open luminaire is recommended for optimum performance in terms of light output and lifespan. Outdoor use only in suitable luminaires.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	80100040401
Brand	Bailey
Productseries	LED Linear
Product type	R7s Slim

ETIM specifications

Nominal voltage [V]	220 - 240
Nominal current [mA]	33 - 33
Power factor	0.8
Lamp power [W]	7.5 - 7.5
Voltage type	AC
Luminous flux [lm]	660 - 660
Rated luminous flux according to IEC 62612 [lm]	660
Lamp efficacy [lm/W]	88
Colour rendering index CRI	80-89
Lamp shape	Tube, double-ended
Filament lamp	No
Type of glass/cover	Clear
Colour of light according to EN 12464-1	Warm white <3300 K
Socket	R7s
Colour	White
Colour temperature [K]	3000 - 3000
Colour housing	Grey
Beam angle [°]	360 - 360
Colour consistency (McAdam ellipse)	SDCM6
Dimmable	No
Diameter [mm]	12
Length [mm]	118
Degree of protection (IP)	IP20
Energy Efficiency Index (EEI)	0.15
Lamp designation	Other
Energy efficiency class	F
Min. number of switching cycles	15000
Weighted energy consumption in 1000 hours [kWh]	8
Average nominal lifespan [h]	25000
Remote operation possible	No
With remote control	No
Photobiological safety according to EN 62471	Other
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No

Alternative articles



142582

LED R7s 28X118 DIM
12W (94W) 1400lm
827 360D



142758

LED R7s Glass
14X118 8W (65W)
900lm 827



145772

LED R7s Glass 17x118
DIM 7.6W (63W) 850lm
827