



E32-CC200R

Fiber optic sensor head, diffuse, M6 cylindrical axial, coaxial, R4 fiber, 2 m cable

Specifications

Sensing method	Diffuse reflective
Shape	Threaded
Size	M6
Application	Object detection
Features	Small spot with lens
Temperature range	-40-70 °C
Sensing distance	900 mm
Cable length	2 m
Bending radius	4 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Top-view
Material sheath	Polyethylene

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color
mark sensor



E3NX-CA

High-performance color
mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3X-NA

Digital fiber amplifier with
potentiometer adjustment



E3NX-FA

High-performance digital
fiber amplifier

Downloads

CAD Library



Fiber Optic Sensors Group Catalogue

EN PDF 7.54 MB

