


SKYTEC® | TRC715

A LIGHTWEIGHT NITRILE FOAM COATED GLOVE WITH STEEL FIBRE AND RECYCLED POLYESTER

Outstanding cut resistance allowing protection in the most risky applications. Breathable, long lasting and flexible glove providing excellent grip in oily conditions

FEATURES

- › Cut resistant: Level E (EN 388:2016)
- › A flexible and comfortable glove offering great dexterity
- › HPPE on the inside provides comfort and protection
- › Fully encapsulated steel and nylon on the outside strengthens the protection against burrs and sharp edges
- › Micro foam nitrile coating gives exceptional grip while allowing warm air and moisture from inside to escape, keeping your hands dry and comfortable
- › Reinforced thumb crotch enhances durability
- › RCS (Recycled Claim Standard) certified
- › 1 pair = 1 PET bottle of 500ml recycled
- › Seamless knit prevents irritation
- › Designed for easy movement and continuous wear



SUITABLE FOR

Typical Industries

- Automotive
- Construction
- Maintenance
- Manufacturing
- Metal Industry

Suitable Applications

- Assembly
- Handling sharp and oily parts
- Machining
- Glass handling
- Bodywork

CERTIFICATION



See overleaf for explanation


TRC715
PRODUCT INFORMATION

MATERIALS	LINER:	13 gauge HPPE, steel fibre, recycled polyester
	COATING:	Foam nitrile
COLOUR	Green/black	
LENGTH (mm)	250 (Size Dependent)	
CUFF STYLE	Elasticated knit wrist	


RECOMMENDATIONS FOR USE

- **USE:** General handling glove with cut protection. Not suitable for thermal, electrical, chemical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

ORDERING DETAILS

SIZE	CODE	PACKAGING
6/XS	SKG00016EB	10 pairs per bag 120 pairs per case
7/S	SKG00016ED	
8/M	SKG00016EF	
9/L	SKG00016EH	
10/XL	SKG00016EJ	
11/XXL	SKG00016EL	

CERTIFICATION LEGENDS

MECHANICAL HAZARDS EN 388:2016 PERFORMANCE LEVELS*


*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter

CLASSIFICATION FOR CUT RESISTANCE

Measured breakthrough time	Permeation performance index (grams)
A1	≥ 200
A2	≥ 500
A3	≥ 1000
A4	≥ 1500
A5	≥ 2200
A6	≥ 3000
A7	≥ 4000
A8	≥ 5000
A9	> 6000

EUROPE
www.globusgroup.com

E: sales@globus.co.uk
T: +44 (0)161 877 4747
F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA
www.globusgroup.com/gcc

E: gcc@globusgroup.com
T: +971 4 882 9962
F: +971 4 882 9963

GLOBUS AMERICAS
www.globusgroup.com

E: americas@globusgroup.com



Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
 Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
 Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

©2022 Globus (Shetland) Ltd | SKY-DATA-TRC715-0723_1