

#### **FEATURES**

- Chrome plated brass ball for longer life
- Compression fitting connection type
- Handle clearly shows ball position
- No metal-to-metal moving parts
- No maintenance ever required

# RS PRO Brass High Pressure Ball Valve 2 Way

RS Stock No.: 486-306



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

RS PRO quarter-turn manual ball valves feature a dual sealing system that allows the valve to be operated in either direction making installation easier. Manual ball valves are used to operate shut off valves which control water flow and pressure. With no metal-to-metal moving parts and a chrome plated ball, the RS PRO manual valves provide simple shut-off functionality for a range of applications such as drinking water, water and plumbing. The manual turn lever can be operated in either direction and features indicating arrows to clearly show the position of the ball and flow of media within the valve. Suitable for domestic water services, heating and air-conditioning plants and compressed air systems.

#### **General Specifications**

Attachment Type	Compression
Body Material	Brass
Compression Fitting Size	22mm
Thread Size	22mm
Safe For Use With	Gas, Oil, Petrol, Water
Туре	2 Way
Application	Heating systems; Water treatment; Liquid flow control

#### **Mechanical Specifications**

Connection Size	22mm

#### **Operation Environment Specifications**

Maximum Working Pressure	16 bar
--------------------------	--------

#### **Approvals**

Compliance/Certifications	WRAS (UK), KIWA-Swedcert (Sweden), GOST-R (Russia), Expert Conclusion (Russia), EAC		
	Conforming (Russia), UkrSepro (Ukraine), RoHS		
	Compliant, ISO 6509		















P/	ART DESCRIPTION	Q.TY	MATERIAL		
1	Unplated body	1	CW602N		
2	Ball seat	2	PTFE		
3	Chrome plated ball	1	CW602N		
4	Unplated end cap	1	CW602N		
5	Olive	2	CW617N		
6	Unplated nut	2	CW617N		
7	Unplated stem O-ring design	1	CW602N		
8	Geomet® nut	1	CB4FF		
9	O-Ring	2	FPM		
10	White PVC coated Geomet® steel handle	1	DD11		








Valve code	S28C12	S28D15	S28D18	S28E22	S28F28	S28G35	S28H42	S28l54
D (mm)	12	15	18	22	28	35	42	54
DN (mm)	10	15	15	20	25	32	40	50
L (mm)	67	72	78.5	79	90.5	110	128.5	142
A (mm)	100	100	100	120	120	158	158	158
H (mm)	38	43	43	50	54	73	79	86
CH (mm)	19	24	27	32	38.5	48	54	70

### **Pressure Drop Chart**



## **Pressure-Temperature Chart**

