


06800020

RCK 80 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06800020
Ød (DD) mm	20
ØD (D) mm	28
D1 (D1) mm	44
D2 (D2) mm	50
L1 (L1) mm	19
L2 (L2) mm	32.5
L3 (L3) mm	39.5
L (L) mm	45.5
Maximum torque Mt (MT) Nm	220
Clamping pressure - Shaft (CPS) N/mm ²	160
Clamping pressure - Hub (CPH) N/mm ²	115
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	4
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x18
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	17.0