



# Solenoid valve JMFH-5-1/8-S-B

Part number: 30487

**FESTO**



 [General operating condition](#)

## Data sheet

| Feature                                               | Value                                                                                      |
|-------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Valve function                                        | 5/2 bistable                                                                               |
| Type of actuation                                     | Electric                                                                                   |
| Construction width                                    | 26 mm                                                                                      |
| Standard nominal flow rate (standardised to DIN 1343) | 1000 l/min                                                                                 |
| pneumatic working port                                | G1/8                                                                                       |
| Operating pressure                                    | -0.09 MPa ... 1 MPa                                                                        |
| Operating pressure                                    | -0.9 bar ... 10 bar                                                                        |
| Design                                                | Piston gate valve                                                                          |
| Nominal size                                          | 8 mm                                                                                       |
| Sealing principle                                     | Soft                                                                                       |
| Mounting position                                     | optional                                                                                   |
| Manual override                                       | Non-detenting                                                                              |
| Type of piloting                                      | Pilot actuated                                                                             |
| Pilot air supply                                      | External                                                                                   |
| Flow direction                                        | Reversible                                                                                 |
| Symbol                                                | 00991016                                                                                   |
| lap                                                   | Overlap                                                                                    |
| Pilot pressure                                        | 0.2 MPa ... 1 MPa                                                                          |
| Pilot pressure                                        | 2 bar ... 10 bar                                                                           |
| Max. switching frequency                              | 3 Hz                                                                                       |
| Switching time reversal                               | 12 ms                                                                                      |
| Max. positive test pulse with 0 signal                | 2200 µs                                                                                    |
| Max. negative test pulse with 1 signal                | 3700 µs                                                                                    |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                        | 1 - Low corrosion stress                                                                   |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L                                                                          |
| Storage temperature                                   | -40 °C ... 60 °C                                                                           |
| Media temperature                                     | -10 °C ... 60 °C                                                                           |
| Pilot medium                                          | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Ambient temperature                                   | -5 °C ... 40 °C                                                                            |
| Product weight                                        | 400 g                                                                                      |
| Electrical connection                                 | Via F coil, to be ordered separately                                                       |
| Type of mounting                                      | On PR rail<br>With through-hole                                                            |

| Feature                      | Value              |
|------------------------------|--------------------|
| Auxiliary pilot air port 12  | G1/8               |
| Auxiliary pilot air port 14  | G1/8               |
| Pilot exhaust port 82        | M5                 |
| Pilot exhaust port 84        | M5                 |
| Pilot air port 12            | G1/8               |
| Pilot air port 14            | G1/8               |
| Pneumatic connection, port 1 | G1/8               |
| Pneumatic connection, port 2 | G1/8               |
| Pneumatic connection, port 3 | G1/8               |
| Pneumatic connection, port 4 | G1/8               |
| Pneumatic connection, port 5 | G1/8               |
| Note on materials            | RoHS-compliant     |
| Material seals               | NBR                |
| Material housing             | Die-cast aluminium |