

KEMET Part Number: C0805C106K9PACTU
(C0805C106K9PAC7800)

SMD Comm X5R, Ceramic, 10 uF, 10%, 6.3 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 0805



Dimensions

| Dimensions | |
|------------|------------------|
| L | 2mm +/-0.2mm |
| W | 1.25mm +/-0.2mm |
| T | 1.25mm +/-0.15mm |
| S | 0.75mm MIN |
| B | 0.5mm +/-0.25mm |

Packaging Specifications

| Packaging Specifications | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2500 |

General Information

| General Information | |
|-----------------------|--|
| Supplier: | KEMET |
| Series: | SMD Comm X5R |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Temperature Stable, Class II |
| Features: | Temperature Stable, Class II |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Note: Referee time for X5R dielectric for this part number is 48 hours |
| Chip Size: | 0805 |
| Shelf Life: | 78 Weeks |
| MSL: | 1 |

Specifications

| Specifications | |
|---|---------------------|
| Capacitance: | 10 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 6.3 VDC |
| Dielectric Withstanding Voltage: | 15.75 VDC |
| Temperature Range: | -55/+85C |
| Temperature Coefficient: | X5R |
| Dissipation Factor: | 10.00% 1kHz 25C |
| Aging Rate: | 5% Loss/Decade Hour |
| Insulation Resistance: | 10 MOhms |