

CL 10000 10.8/18.0

LED cordless building site spotlight 10,8/18,0 V

Order no. 504610

GTIN 4030293230538

- + Powerful 10000 lumen battery-powered building site spotlight with 5 brightness levels plus ECO mode. With memory function, the light starts at the last set level
- + The colour temperature of 5000 kelvin corresponds to a neutral light colour and is ideal for work in dark rooms. This enables an accurate adjustment to the job in hand
- + Lamp can be turned through 215°
- + Visual early-warning system: low battery charge is indicated by slightly decreasing level of brightness
- + 5/8" connection thread for tripods
- + Integrated spacer elements with cooling openings protect the lens and surfaces
- + With optional wall fastening
- + Rugged and long-life for heavy-duty use
- + LED battery capacity display
- + FLEX battery system: suitable for all FLEX 10,8 V and 18,0 V battery packs. Delivery does not include battery and charger



Technical data

Battery voltage	10.8 / 18.0 V
Battery capacity	2.5 / 4.0 / 5.0 / 8.0 Ah
Luminous flux	(10.8V) 300 / 1000 / 3000 (18V) 300 / 1000 / 3000 / 5000 / 7000 / 10000 lm
Protection class	IP65

Standard equipment