

TECHNICAL SPECIFICATION



EVOGuard®C5-MAX Industrial Visor

EVOGuard®C5-MAX / ADA280-070-000



DESCRIPTION

EVOGuard®C high performance industrial visors provide comprehensive facial coverage without limiting movement. The optical class 1 visor range offers UV protection and a panoramic view with minimal distortion.

Compatible with *EVO® helmet models, the C5-MAX visor offers up to AT rated impact and features an integral chinguard for added coverage. The EVOGuard® C5 Max should be used as part of an arc flash protective ensemble that also includes suitable arc flash protective clothing and gloves.

*Excluding EVO®6100 range.

OPTIONS

EVOGuard®C5-MAX (ADA280-070-000)

EVOGuard® C5-MAX Industrial Visor Kit K&N – EVO® VISTA® Compatible (ADA280-070-00C)

SAFETY STANDARDS

EN 166 • EN 170 • GS-ET-29



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 1 of 3 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.



SPECIFICATIONS



RADIATION PROTECTION BREAKDOWN filtering effect
Scale Number
2C



LIGHT TRANSMISSION BREAKDOWN Lens Shade number
1.2



Manufacturer's Trademark
JSP Dagger



Optical Class (1 – Class 1 – High quality for regular use. 2 – Class 2 – Medium quality for occasional use. 3 – Class 3 – Low quality for exceptional use)
1



High Energy Impact resists a 6 mm, 0.86g ball @ 190 m/s
Maximum protection for face shields
A - Only to be fitted to EVO® helmets



The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures. (-5°C and +55°C) Optional
T



Protection from Liquid Splash
3



Protection Against Short Circuit Electric Arc
8

Arc Flash Protection Class
1: Up To 4kA, or 155kJ/m² or 3.7cal/cm²



Resistance to Molten Metals and Hot Solids Helmets (optional)
9



Visible Light Transmittance (VLT)
0: ≥ 75%



Resistance to fogging (optional)
N



Resistance to Surface Damage by Fine Particles (optional)
K



BSI Kitemark
Yes



Visor Length
21.5cm



Product Weight
216g

Material
Polycarbonate Shield



Kit
Supplied With: EVO®2,3,5,DS,Lite,Skyworker™ Arms. EVO8/EVOLite Badgeholder Arms.



Recyclable
Yes

Lens Thickness - centre
2.00mm

Lens Thickness - edge
1.70mm

UI
https://www.jspgo.com/UI-HD/UI_EVOGuard/UI-Pages/InstructionImages.png

FEATURES



Compatibility

EVOGuard® visors maximise compatibility with JSP half masks, disposable respirators, prescription glasses and the Sonis® helmet mounted ear defender range.



Vision

The optical class 1 visor offers a panoramic view with minimal distortion, ideal for comfortable all day wear.



Impact

Wide range of high performance visors offering up to A rated impact resistance when fitted to a safety helmet and medium energy impact protection with the EVOGuard® browguard.



Coverage

EVOGuard® visors provide comprehensive facial coverage without limiting movement. EVOGuard® MAX visors offer enhanced coverage with an integral chinguard.



Electric Arc Protection

EVOGuard® C5 MAX meets the requirements of GS-ET-29, providing eye and face protection against a risk of a fault arc: GS-ET-29 Class 1, 4kA (155kJ/m²) and 3.7 Cal/cm².



UV Protection

Visor filters harmful UV radiation to protect the eyes whilst also offering high light transmission and enhanced colour recognition.



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspgo.com / Web: www.jspgo.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspgo.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 3 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.





 www.youtube.com/watch?v=_VnTgBRRT9E

DOWNLOADS

 [Image Pack \(ZIP\)](#)

 [doc-evoguard.pdf \(PDF\)](#)



JSP Limited. Worsham Mill. Minster Lovell. Oxford OX29 0TA. England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 3 of 3 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

