



Features

• SylWork offers a range of high-performance LED work lights, available in both mains-powered and battery-operated models. Designed for maximum versatility, SylWork provides reliable, temporary lighting for a variety of DIY projects, including home decorating, household repairs, cleaning, tidying, and general maintenance tasks. The SylWork Flood Rechargeable is a battery-operated floodlight, ideal for worksite tasks, maintenance work, camping, and outdoor activities. Designed for convenience, it features a built-in hook for hands-free use and offers up to four hours of operating time with a two-step dimming function for adjustable brightness. Emitting a 4000K cool white light, it provides clear, balanced illumination for any task. Additionally, it doubles as a power bank, allowing you to charge mobile devices. Built for durability and practicality, it fully charges in just four hours and comes with a three-year warranty.

Product Overview

Product name	SylWork Flood Rechargeable
Technology	LED
Cap/Base	N/A
Housing	ABS Plastic
Mount	Other
General application	Residential & Consumer
ETIM Class	EC000694
Fixture luminous flux (lm)	900
Correlated colour temperature (k)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	110
Photobiological Risk Group	RG1

SylWork Flood Rechargeable 0090204

Total power consumption (W)	10
Electrical protection	Class III
Control gear type	Not required
Dimmable	No
Housing colour	Black
IP rating	IP54
IK rating	IK06
Product EAN number	5410288902043
Warranty	3 years
Dimming method	N/A

Data table

GENERAL DATA

Product name	SylWork Flood Rechargeable
Technology	LED
Cap/Base	N/A
Housing	ABS Plastic
Mount	Other
General application	Residential & Consumer
Operating temperature range (°C)	-10°C...+35°C
ETIM Class	EC000694
Warranty	3 years

OPTICAL DATA

Fixture luminous flux (lm)	900
Correlated colour temperature (k)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	110
Distribution type	None
Photobiological Risk Group	RG1

ELECTRICAL DATA

Total power consumption (W)	10
Current (A)	2
THD (at 230 V, 50 Hz, full load, at 100% dimming level) \leq xx.x %	1
Electrical protection	Class III
Control gear required	No
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Nominal Frequency (Hz)	DC
Max. products per 10A C Breaker	1
Max. products per 16A C Breaker	1

LIFETIME DATA

Lifespan L70 B50	30000
------------------	-------

PHYSICAL DATA

Housing colour	Black
IP rating	IP54
IK rating	IK06
Diffuser finish	Opal
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	178
Nominal Product Width (mm)	129
Nominal Product Height (mm)	44
Weight (kg)	0.56

PACKAGING

Product EAN number	5410288902043
Packaging single length / height (cm)	13.5
Packaging single width (cm)	5.4
Packaging single depth (cm)	18.5



SylWork Flood Rechargeable
0090204

DUN14 (inner)	15410288902040
Units per outer package	1
Packaging outer length / height (cm)	13.5
Packaging outer width (cm)	5.4
Packaging outer depth (cm)	18.5

SAFETY DATA

Glow Wire Test (°C)	650
Optimal operating condition (°C)	-10-35
Special purpose lamp	No
Dry applications use only	No
Suitable for household illumination	No