


- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER ASTM D5138 LCPO00 G30A 32250, COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR-BRONZE.
- 3 CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) -
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290.
ON MATING SURFACES-
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA UNCONTROLLED ENVIRONMENT
ON LEADS-
0.0006 MIN TIN PER ASTM B 545, OVER UNDERPLATE
LUBRICATION (MIN MATING SURFACES)
SURFACE CONDITIONER AFTER PLATING.
- 4 PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- 5 CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) -
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290.
ON MATING SURFACES-
0.00076 MIN NICKEL OR COBALT HARDENED GOLD PER ASTM B-488 OVER UNDERPLATE.
ON LEADS-
0.0006 MIN TIN PER ASTM B 545, OVER UNDERPLATE
LUBRICATION (MIN MATING SURFACES)
SURFACE CONDITIONER AFTER PLATING.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	NO	46	23	47.88	3	96	3-5536511-3
	NO	22	11	23.88	5	48	3-5536511-2
OBSOLETE	YES	10	5	11.88	3	24	3-5536511-1
	NO	34	17	35.88	3	72	1-5536511-2
OBSOLETE	NO	130	65	131.88	3	264	1-5536511-1
	NO	106	53	107.88	3	216	1-5536511-0
OBSOLETE	NO	118	59	119.88	3	240	5536511-9
	NO	82	41	83.88	3	168	5536511-8
OBSOLETE	NO	66	33	67.88	3	136	5536511-7
	NO	58	29	59.88	3	120	5536511-6
OBSOLETE	NO	70	35	71.88	3	144	5536511-5
	NO	94	47	95.88	3	192	5536511-4
OBSOLETE	NO	46	23	47.88	3	96	5536511-3
	NO	22	11	23.88	3	48	5536511-2
OBSOLETE	YES	10	5	11.88	3	24	5536511-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER CHK R. WERTZ APP'D R. WERTZ	31AUG04 31AUG04 31AUG04	STE TE Connectivity																													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RCPT. ASSY, SIGNAL MODULE, Z-PACK 2mm FB 4 ROW, 3.55mm PRESS FIT LEAD LENGTH																													
<table border="1"> <tr><td>0</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>1</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>2</td><td>PLC</td><td>±</td><td>.13</td></tr> <tr><td>3</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>4</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td colspan="2">ANGLES</td><td>±</td><td>-</td></tr> <tr><td colspan="2">FINISH</td><td>±</td><td>-</td></tr> </table>		0	PLC	±	-	1	PLC	±	-	2	PLC	±	.13	3	PLC	±	-	4	PLC	±	-	ANGLES		±	-	FINISH		±	-	APPROXIMATE WEIGHT		RESTRICTED TO	
0	PLC	±	-																														
1	PLC	±	-																														
2	PLC	±	.13																														
3	PLC	±	-																														
4	PLC	±	-																														
ANGLES		±	-																														
FINISH		±	-																														
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO																													
1/2		3/5		A1 00779 C=5536511																													
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1 REV D																													

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)