




VAL-U-LOK

TE Internal #: 1586768-8
PCB Mount Header, Vertical, Wire-to-Board, 8 Position, 4.2 mm [.165 in] Centerline, Fully Shrouded, Tin (Sn), Through Hole - Solder, Power, White, Bag

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **8**
Number of Rows: **2**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Loaded Positions	8
Number of Power Positions	8
PCB Mount Orientation	Vertical
Number of Positions	8
Number of Rows	2

Electrical Characteristics



Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Layout	Matrix
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	9 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Keyed
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polyamide
Centerline (Pitch)	4.2 mm[.165 in]

Dimensions

Row-to-Row Spacing	4.2 mm[.165 in]
Connector Width	9.75 mm[.384 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	12.8 mm[.504 in]
Connector Length	18 mm[.709 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
-----------------------------	----------------



Operating Temperature Range

-40 – 105 °C[-40 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	315
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2296207-8
8P PM PLUG VAL-U-LOK PM GWT/V0

TE Part # 2-2825272-0
20P VERT HDR VAL-U-LOK HCS GW

TE Part # 1586862-8
8P FH PLUG VAL-U-LOK FH GW

TE Part # 1586861-8
8P PM PLUG VAL-U-LOK PM GW

TE Part # 2825272-8
8P VERT HDR VAL-U-LOK HCS GW

TE Part # 1-2825272-6
16P VERT HDR VAL-U-LOK HCS GW

TE Part # 2296206-8
8P FH PLUG VAL-U-LOK FH GWT/V0

Customers Also Bought

TE Part #1586768-4
4P VERT HDR VAL-U-LOK GW

TE Part #5-103735-2
03 MTE HDR SRST LATCH .100CL

TE Part #1-406541-1
MJ,INV,1X1,6PNL G,.100"ST,SN


TE Part #5-103735-1
02 MTE HDR SRST LATCH .100CL

TE Part #2-328527-1
TERMINAL,PG R 16-14 8

TE Part #3-640443-2
02P MTA100 CONN ASSY GRN

TE Part #3-520117-2
ULTRAFast 250 ASSY REC 16-14 TPBR LP

TE Part #104257-5
06 MTE RCPT HSG SR LATCH .100



Documents

Product Drawings

8P VERT HDR VAL-U-LOK GW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1586768-8_B_c-1586768-8-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1586768-8_B_c-1586768-8-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1586768-8_B_c-1586768-8-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

VAL-U-LOK_GLOW_WIRE_CONNECTORS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

VDE Certificate

English