



Technical data

4T-07079/07196


Single row tapered roller bearings

Tapered roller bearing, pressed steel cage


KIT CONTENT

4T-07079, 4T-07196

VISUAL (S)



4T-07079/07196
Single row tapered roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	20 mm
D - External diameter	50,005 mm
B - Bearing/Inner ring width	14,26 mm
C - Outer ring width	9,525 mm
T - Total width	13,495 mm
a - Charge load application point	16,5 mm
rs - Min fillet radius	1,5 mm
r1s - Min fillet radius	1 mm
Mass	0,138 kg

PRODUCT PERFORMANCE

C - Dynamic load	28,9 kN
C0 - Static load	27,9 kN



PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.4
Y0 - Static axial load coefficient	0.82
Y2 - Upper axial load coefficient	1.49
N lim - Oil lubrication limit speed	10000 tr/min
N lim - Grease lubrication limit speed	7500 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	26 mm
db min - Min IR shoulder diameter	27,5 mm
Da max - Max shoulder diameter OR	47 mm
Db min - Min OR shoulder diameter	44,5 mm
ra max - Max fillet radius	1,5 mm
r1a - Max fillet radius	1 mm

KIT COMPONENT

Cone designation	4T-07079
Cup designation	4T-07196

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-07079/07196
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X_o	Y_o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

