Drywall Screwdriver LXT®

DFS250

18V • 0 – 2 500 min^{-1}

Reliable brushless screwdriver

A brushless screwdriver with auto-stop and start. An ergonomic design and rubberised handle ensure good grip. Precise depth control and a speed of 2 500 min^{-1}, adjustable from the switch. Equipped with an LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Capacity Drywall Screw	5 mm
No load speed	0 - 2500 min^{-1}
Sound Pressure Level (L_{pA})	75 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,9 kg
Product Dimensions (L x W x H):	259 x 79 x 259 mm
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Driving Shank	1/4 "
Vibration Level, Screwdriving Without Impact	≤ 2,5 m/s^2
Vibration Uncertainty (K Factor), Screwdriving Without Impact	1,5 m/s^2

User benefits

- Brushless maintenance-free and long-life motor
- Ergonomic soft grip handle provides increased comfort
- Reversing switch
- Used for hexagonal screws
- Depth adjustment
- Built-in LED light with afterglow function illuminates the work area
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com

Related products

Optional AC

191L24-0
Autofeed Attachment, 25-55 mm



Other

User manual

Parts drawing