



Solid Grommet, Natural, Adh., PE, 1.6mm Max Panel, 30.5m L, PK1

GES62F-A-C

The GES62F-A-C Polyethylene Solid Grommet Edging protects and prevents wires and cables from chafing against sharp edges of panel walls and knockouts. Solid edging recommended for use on straight edges only. The material is highly flexible, while the adhesive lining ensures the product will stay in place. Packaged on a 100' (30.5m) reel for easy handling and dispensing. Polyethylene. Designed for 0.036" - 0.062" (0.9mm - 1.6mm) thick panels. Color Natural. 1 per package.

Specifications

| | |
|--|--|
| Note | Designed for straight edges |
| Product Type | Solid Grommet Edging |
| Color | Natural |
| Material | Polyethylene |
| Maximum Compatible Panel Thickness (In.) | 0.06 |
| Maximum Compatible Panel Thickness (mm) | 1.6 |
| Minimum Compatible Panel Thickness (In.) | 0.036 |
| Minimum Compatible Panel Thickness (mm) | 0.9 |
| Maximum Operating Temperature (°C) | 50 |
| Maximum Operating Temperature (°F) | 122 |
| Minimum Operating Temperature (°C) | -40 |
| Minimum Operating Temperature (°F) | -40 |
| Overall Length (ft.) | 100 |
| Overall Length (m) | 30.48 |
| Overall Width (In.) | 0.13 |
| Overall Width (mm) | 3.3 |
| Overall Height (In.) | 0.16 |
| Overall Height (mm) | 4.1 |
| Resistance Properties | Abrasion-Resistant |
| Standards Met | RoHS Compliant |
| Application | To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts. |
| Part Features | Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes. |

Packaging Detail

| | |
|-----------------------|-------------|
| UPC | 07498340559 |
| Std. Pkg. Qty. | 1 |
| Std. Pkg. Volume (cf) | 0.1339 |
| Std. Ctn. Qty. | 0 |
| Std. Ctn. Volume (cf) | 0.0000 |