



Quick-Build™ QB-MOUNT-L Harness Board Accessory, Black, PA 6.6, 1x1.05", PK50

QB-MOUNT-L

Panduit QB-MOUNT-L Harness Board Pegs can be positioned and relocated. They allow accessories to rotate as needed even after mounting pegs have been installed into grid tile. For use with Quick-Build™ single nail holders and five nail holders and Quick-Build™ mounting platforms. Pegs are 2.2" x 1" x 1.05" (55.9 x 25.4 x 26.7 mm) in size and come in packages of 50.

Specifications

Product Type	Mount
Sub Brand	Quick-Build™
Color	Black
For Use With	Use with Quick-Build™ Nail Holders, Quick-Build™ Wire End Holders, Quick-Build™ Replaceable Elastic Retainers, and Quick-Build™ Mounting Platforms
Material	Nylon 6.6
Overall Length (In.)	1
Overall Length (mm)	25.4
Overall Width (In.)	1.05
Overall Width (mm)	26.7
Overall Height (In.)	2.2
Overall Height (mm)	55.9
Standards Met	RoHS Compliant
Static Load Capacity (kg)	2.2
Static Load Capacity (lb)	5
Application	(1) To Create a Harness on Top of a Drawing(2) Repositionable to Allow User to Build Different Harness Configurations as Needed
Part Features	Repositionable to allow user to build different harness configurations as needed, Pointed end inserts through drawing secured to grid tiles, providing the ability to create a harness on top of a drawing

Packaging Detail

UPC	07498308302
Std. Pkg. Qty.	50
Std. Pkg. Volume (cf)	0.1326
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	1.3262