

## **FEATURES**

- 3 mm coloured diffused epoxy lens
- 2 mm x 0.5 mm blade terminations
- Solder tab blade terminals
- Connection tabs are colour coded for polarity (gold +ve, silver -ve)
- Various voltage ratings

# RS PRO Green Indicator, 24 V dc, 6mm Mounting Hole Size, Solder Tab Termination

RS Stock No.: 206-019



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



**Product Description** 

Brought to you by RS Pro, a range of high quality indicators. These LED indicators are an excellent solution to applications which require a signal or warning light. The build quality of each indicator and LED provides a high level of brightness and longevity at low level consumption. Each indicator includes a convenient solder lug, meaning they can be terminated through a quick and easy installation for your application. All models are highly reliable and excellent quality.

#### **General Specifications**

Light Output Colour	Green
Lamp Type	LED
Termination Type	Solder Tab
Туре	Panel Mount
Bezel Style	Recessed
Bezel Colour	Black Chrome
Intensity	40mcd
Type Of Illumination	Fixed Light
LED Colour	Green
Viewing Angle	30° to 100°
Life Expectancy	100000hours
Applications	Fixed to PCB circuit boards mounted; Switches; Pushbuttons; Used as vehicle indicators

#### **Electrical Specifications**

Voltage Rating	24V dc
Current Rating	20mA
Voltage Tolerance	10%

# Indicators



### **Mechanical Specifications**

Mounting Hole Size	6mm
Length	34.4mm
Torque	4cNm
Lamp Size	3mm

Operation Environment Specifications	
Temperature Rating	-40°C to 85°C

Approvals	
Compliance/Certifications	EN61340





### TECHNICAL SPECIFICATIONS

Voltage	Operating Voltage	<b>Operating Current</b>
	(Min to Max)	(Typical All Types)
02 (No Resistor)	1.8 to 3.8VDC	20mA max*
6VDC	5.4 to 6.6VDC	20mA
12VDC	10.8 to 13.2VDC	20mA
24VAC/DC	21.6 to 26.4VDC	20mA
28VDC	25.2 to 30.8VDC	20mA

Max Reverse Voltage: 5V	
Viewing Angle: 30-100° (deper	ndant on model)
Life Expectancy: 100,000 hour	S
Temperature Range: -40 to +	85°C (operating & storage)
Torque: 4cNm	
PANEL CUTOUT	8,00 [ 0,315 ] AF 2,00 [ 0,079 ] 2,00 [ 0,079 ] M6 x 0,50 THREAD

Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage
HE Red	40mcd	10mcd	2.0V
Green	50mcd	12mcd	2.2V
Yellow	30mcd	6mcd	2.1V
Blue	1,200mcd	100mcd	3.8V
White	1,200mcd	160mcd	3.8V
Orange	60mcd	10mcd	2.0V
Bi-color (Typical) (Red/Green)	20/15mcd	10/8mcd	2.0V/2.2V
The	color is changed by reversing the po	plarity of the supply vol	ltage.
Super Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	1,000mcd	700mcd	2.2V
Green	1,200mcd	2,000mcd	3.5V
Velleur			
Yellow	2000mcd	8,000mcd	2.3V
Blue	2000mcd 1,600mcd	8,000mcd 200mcd	2.3V 3.3V

Hyper Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	3,700mcd	600mcd	2.2V
Green	2,000mcd	350mcd	3.2V
Yellow	1,200mcd	140mcd	2.0V
Orange	4,500mcd	400mcd	2.2V

Luminous intensity will be reduced with lower operating current.

## Indicators



#### RECESSED BEZEL













