

# Actuator

51-  
274.0252

Distribution by  
Rs-online



<https://rs-online.eao.com/p/51-274.0252>

Your product:

---



## 51-274.0252

### Actuator

#### FRONT

|                       |         |
|-----------------------|---------|
| Front dimension:      | Ø 18 mm |
| Front form:           | Round   |
| Front bezel colour:   | Black   |
| Front bezel material: | Plastic |

#### MOUNTING

|                |                |
|----------------|----------------|
| Design:        | Raised         |
| Mounting type: | Panel mounting |

#### OPERATING-/INDICATION PART

|                    |             |
|--------------------|-------------|
| Lens illumination: | Illuminated |
|--------------------|-------------|

#### ELECTRICAL CHARACTERISTICS

|                                          |                                                                                                                                                                                                                                                                                                                                     |
|------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switching voltage and switching current: | 250 VAC, 5 A (ohmic)<br>250 VAC, 3 A (Soldering terminal)<br>250 VAC, 2 A (inductive, $\cos(\phi) = 0.7$ )<br>125 VAC, 3 A (inductive, $\cos(\phi) = 0.7$ )<br>220 VDC, 0.1 A (inductive, L:R = 30 ms)<br>110 VDC, 0.2 A (inductive, L:R = 30 ms)<br>60 VDC, 0.7 A (inductive, L:R = 30 ms)<br>24 VDC, 2 A (inductive, L:R = 30 ms) |
| Contacts:                                | 4 NC / 4 NO                                                                                                                                                                                                                                                                                                                         |
| Rated Operational Voltage Ue:            | 250 VAC/DC according to EN IEC 60947-1                                                                                                                                                                                                                                                                                              |
| Switching rating:                        | 250 V @ 3 A                                                                                                                                                                                                                                                                                                                         |
| Electrical lifetime:                     | 50 000 cycles of operation                                                                                                                                                                                                                                                                                                          |
| Electric strength:                       | 2500 VAC, 50 Hz, 1 min. between all terminals and earth, according to IEC 61058-1, part 15                                                                                                                                                                                                                                          |

|                                        |                                                                                                                        |
|----------------------------------------|------------------------------------------------------------------------------------------------------------------------|
| <b>Protection class:</b>               | II                                                                                                                     |
| <b>Standards:</b>                      | According to EN/IEC 61058-1                                                                                            |
| <b>Thermal current I<sub>th</sub>:</b> | The maximum current in continuous operation and at ambient temperature not exceeding the quoted maximum values.<br>3 A |

## MECHANICAL CHARACTERISTIC

|                             |                                                                                                                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Terminal:</b>            | Soldering terminal                                                                                                                                                                   |
| <b>Contact material:</b>    | Gold                                                                                                                                                                                 |
| <b>Switching action:</b>    | Maintained                                                                                                                                                                           |
| <b>Switching system:</b>    | Snap-action switching element                                                                                                                                                        |
| <b>Switching system:</b>    | Self-cleaning, double-break snap action switching system, 1 normally closed and 1 normally open contact per element.                                                                 |
| <b>Mechanical lifetime:</b> | 1 Mil. cycles of operation                                                                                                                                                           |
| <b>Operating force:</b>     | 1,8 ... 6 N, depending on the number of switching elements                                                                                                                           |
| <b>Operating Travel:</b>    | 3 mm                                                                                                                                                                                 |
| <b>Tightening torque:</b>   | Fixing nut max. 0.5 Nm                                                                                                                                                               |
| <b>Wire cross section:</b>  | Snap-action switching element with tinned soldering terminals at the sides<br>Max. wire diameter 2 wires à 1.2 mm<br>Max. wire cross-section of stranded cable 1 x 1 mm <sup>2</sup> |
| <b>Weight:</b>              | 0.012 kg                                                                                                                                                                             |

## AMBIENT CONDITION

|                               |                                                                                                          |
|-------------------------------|----------------------------------------------------------------------------------------------------------|
| <b>IP front protection:</b>   | IP65, according to DIN EN 60529                                                                          |
| <b>Operating temperature:</b> | – 25 °C ... + 55 °C, mounted as a block, make sure the heat can escape freely                            |
| <b>Storage temperature:</b>   | – 40 °C ... + 85 °C                                                                                      |
| <b>Shock resistance:</b>      | 15 g for 11 ms, as per DIN / EN 60512-4-3, DIN / EN 60068-2-27 (Single impacts, semi-sinusoidal)         |
| <b>Vibration resistance:</b>  | 10 g at 10 Hz...1500 Hz, amplitude 0.75 mm (Sinusoidal), according to DIN EN 60512-4-4, DIN EN 60068-2-6 |
| <b>Climate resistance:</b>    | Standard condition, as per DIN EN 60068-2-30<br>Changing condition, as per DIN EN 60068-2-14             |

## CERTIFICATE

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| <b>Approbations:</b> | CB (IEC 61058-1), CQC, CSA, DNV, EAC, ENEC (EN 61058-1), UL, VDE            |
| <b>Conformities:</b> | CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 30 / EU (EMC), 2014 / 35 / EU (LVD) |

**REACH:** REACH compliant

**RoHS:** RoHS compliant


## OTHER

**Short Description:** Actuator, Ø 18 mm, Illuminated, Round, Black, Plastic, 4 NC / 4 NO, Maintained, Soldering terminal, IP65, according to DIN EN 60529


**Internal size:** Ø 15,8 mm

**Housing colour:** Black


**Wiring diagrams:**



**Mounting cut-outs:**



**Dimension drawings:**



A = Solder terminal  
B = Plug-in terminal 2.8 mm x 0.5 mm  
C = Universal terminal 2.0 mm x 0.5 mm  
D = Universal-Solder terminal