### Honeywell | Safety Products






PRODUCT NUMBER: 1005598

## Honeywell 5161 ML - FFP1 NR D - AV with valve

Honeywell



#### **Reference Number**

1005598

#### **Product Type**

Respiratory Protection

#### Range

Disposable APR

#### Line

Moulded masks

#### Brand

Honeywell

#### Brand formerly known as

WILLSON

#### Industry

IndustryGlass Industries

#### **Product Use**

**Application**: Aluminium smelting, electronic, glass industries, electrolysis, battery manufacture, swimming-pool maintenance, etc ... Protects against dusts, mists and fumes containing calcium carbonate, clay, kaolin, cellulose, cotton, flour, ferrous metals, vegetal and mineral oils, metal-working fluids (*this list is non-exhaustive*). In case of exposure to levels of acid gases and vapours below WEL\* (hygrogen fluoride, chlorine, hydrochloric acid, etc ...), offers reduction of the nuisance due to odours.

**Maximum usage level**: can be used in atmospheres containing solid and/or liquid aerosols in concentrations up to 4 x WEL\*: FFP1 class (low toxicity). "NR" (Non Reusable) marked, it can be used one single shift (according to EN 149:2001+A1:2009). Certain restrictions or limitations may apply in the case of specific contaminants. Please refer to applicable health and safety standards.

#### Limitation to use:

This single-use filtering half-mask should NOT be used in the following situations :

- oxygen concentration is less than 17% (oxygen-deficient atmospheres)
- contaminants or their concentrations are unknown or are immediately dangerous to life or health
- contaminants concentrations exceed levels fixed by applicable health and safety standards or 4 x WEL\*
- in the presence of toxic or radio-active contaminants
- in the presence of gases or vapours which concentrations exceed WEL\*
- fire fighting.

#### Caution:

We recommend users to ensure that the level of protection offered by the respirator is sufficient for the type and concentration of contaminant(s) in the work area.

For use only by trained and qualified personnel.


Leak-tightness is unlikely to be achieved if the mask is worn against a beard or facial stubble.

This respirator does not supply oxygen.

\* WEL: Workplace Exposure Limit.

#### **Feature**

Rigid shell: shape maintained even in moistened and heavy loading environments. Ultra-soft



hypoallergenic Willtech™ flange seal with absorption properties and a tight sealing film. Large internal volume to easily communicate and breathe. Pre-formed and coloured nosebridge to save time to adjust the mask and to instantly identify its protection level. Shielded exhalation valve with an exclusive design for an improved protection. Twin elastic straps, ultra flexible and strong, stapled outside of the filtering area to avoid any risk of leakage. No latex, no silicone, nor PVC. Lightweight respirators (18g). Dolomite tested.

#### Benefit

Protection and wearer acceptance guaranteed during periods of extended use. Added safety offered. Exceptional level of comfort. Prevents irritation. No risk of allergies. No need to change the respirator for the normal period of use. Environment-friendly.

# **Technical Description** FFP1 Valve Yes Yes Yes

#### Standard

EN149.2001

#### Mask Type

Molded Cup

#### **Protection Class**

#### **Straps**

Double elastics

#### Mask Size

Medium

#### **Latex Free**


#### **PVC Free**

#### Silicone Free

Yes



# FFP1 NR D - AV with valve - Honeywell 5161 ML - 1005598 Certifications EN 149:2001+A1:2009 We're sorry, there are no images available at this time.



© Honeywell International Inc.