

PRODUCT-DETAILS

B14-PS-M

NON-INS PRL SPLICE, 16-14, CMA 2,05



General Information

Extended Product Type	B14-PS-M
Product ID	7TAI029620R0020
EAN	5415022323504
Catalog Description	NON-INS PRL SPLICE, 16-14, CMA 2,05
Long Description	Non-Insulated Parallel Splice, Length .315 Inches, Outer Diameter .155 Inches, Inner Diameter .113 Inches, Wire Range #16-#14 AWG 2,050kcmi-5,180kcmil, Copper, Tin Plated

Ordering

EAN	5415022323504
UPC	786210936260

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	2.75 in 70 mm
Package Level 1 Height	2.25 in 57 mm
Package Level 1 Depth / Length	3.25 in 83 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	6.25 in 159 mm

Package Level 2 Height	3.75 in 95 mm
Package Level 2 Depth / Length	12.5 in 318 mm

Additional Information

Brand / Label	Sta-Kon
Color	Metallic
Effective Date	20040819
Material	Copper
Number of Batteries	0
Product Name	ELECTRICAL SPLICE,<1000V
Product Type	Non-Insulated Parallel Splice
Special Functions	Resistant to corrosion and preserve the electrical integrity of the wires in single or multiple strands. Feature an intelligent constructable part number for quick identification of the wire range.
Standards	UL E9809
Surface Finishing	Tin Plated
Voltage Rating	600 V

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	B14-PS-M
Instructions and Manuals	B14-PS-M

Classifications

ETIM 6	EC001059 - Crimp splices for copper conductor
ETIM 7	EC001059 - Crimp splices for copper conductor
UNSPSC	39121449
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4669 >> Wire or cable compression splice

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

