

# Product data sheet

Specifications



## Floor standing enclosure polyester vers.PLA completely sealed 1500x750x420 IP65

NSYPLA1574G

### Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLA
Nominal height	1500 mm
Nominal width	750 mm
Nominal depth	420 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door

### Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Plain front
Number of doors	1 door(s)
Door opening side	Reversible (120 °)
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Front Rear
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
NEMA degree of protection	NEMA 1 NEMA 3S NEMA 13 NEMA 5 NEMA 3R NEMA 12 NEMA 2 NEMA 3X

NEMA 3

**Product certifications** DNV Marine  
Veritas  
UL/cUL listed

**Electrical insulation class** Class II

## Environment

**IP degree of protection** IP65 conforming to IEC 60529 (completely sealed)

**IK degree of protection** IK10 conforming to IEC 62262 (plain door)

**Fire resistance** 960 °C conforming to IEC 62208

**Ambient air temperature for storage** -35...90 °C

## Packing Units

**Unit Type of Package 1** PCE

**Number of Units in Package 1** 1

**Package 1 Weight** 41.944 kg

**Package 1 Height** 45.0 cm

**Package 1 width** 78.0 cm

**Package 1 Length** 150.0 cm

**Unit Type of Package 2** PAM

**Number of Units in Package 2** 2

**Package 2 Weight** 120.726 kg

**Package 2 Height** 165.0 cm

**Package 2 width** 100.0 cm

**Package 2 Length** 120.0 cm

## Offer Sustainability

**Sustainable offer status** Green Premium product

**REACH Regulation** [REACH Declaration](#)

**EU RoHS Directive** Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

**Mercury free** Yes

**RoHS exemption information** [Yes](#)

**China RoHS Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

**Environmental Disclosure** [Product Environmental Profile](#)