





FAG

6020-Z

Deep groove ball bearing

Deep groove ball bearing 60...-Z, single row, shield , steel sheet metal cage

Technical information



Your current product variant

Sealing	Z	Non-contact shield on one Side
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	100 mm	Bore diameter
D	150 mm	Outside diameter
B	24 mm	Width
C _r	64,000 N	Basic dynamic load rating, radial
C _{0r}	54,000 N	Basic static load rating, radial
C _{ur}	3,050 N	Fatigue load limit, radial
n _G	6,100 1/min	Limiting speed
n _{gr}	5,100 1/min	Reference speed
≈m	1.33 kg	Weight



Mounting dimensions

$d_{a\min}$	107 mm	Minimum diameter shaft shoulder
$D_{a\max}$	143 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1.5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1.5 mm	Minimum chamfer dimension
D_1	134.12 mm	Shoulder diameter outer ring
D_2	137.3 mm	Caliber diameter outer ring
d_1	116.2 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Calculation factors

f_0	15.8	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Sealed on one side